


REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	G	PLATING CHANGE FROM BRIGHT TIN TO MATTE TIN	28MAR2023	KA	SPS



NOTES:

- 1 CONTACT MATERIAL: PHOSPHOR BRONZE
- 2 PLATING: UNDER COATING 1,3 $\mu$ m Ni OVERALL  
AT CONTACT PLACE 0,8 $\mu$ m Au  
AT CRIMP BARRELS 2,5 $\mu$ m Sn
- 3 CONTACT POINT
- 4 BOTTOM OF CONTACT TO BE STRAIGHT AFTER CRIMPING OF WIRE
- 5 WIRE RANGE: 0,08–0,22mm<sup>2</sup>  
INSULATION RANGE: 0,80–1,50 DIA.
- 6 OPTIONAL
- 7 THE CONTACT MEETS THE REQUIREMENT OF INTERNATIONAL STANDARD IEC 603–8

LOOSE PIECE	2	1	182734–3
STRIP	2	1	188746–1
CONFIGURATION	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JJ DESPRETZ 22–NOV–04	TE Connectivity	
DIMENSIONS: mm		CHK T CORRIOU		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Y PETRONIN	HE 1302 CONNECTOR (GOLD VERSION) CRIMP CONTACT (AWG 28–24)	
0 PLC ± –		PRODUCT SPEC	SIZE	
1 PLC ± 0.3		APPLICATION SPEC	CAGE CODE	DRAWING NO
2 PLC ± –		WEIGHT	RESTRICTED TO	
3 PLC ± –		–	A3	00779
4 PLC ± –		–	C=188746	
ANGLES ± 1°		–	SCALE 1:1	
MATERIAL		–	SHEET 1 OF 1	
FINISH		–	REV G	
–		–	CUSTOMER DRAWING	

