






REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REVISED PER ECR-20-010049	14DEC2020	BH	E.W



RECOMMENDED MATING TAB DESIGN
 (FINISH) PLAIN OR ELECTRO-TIN
 (MATERIAL) 70/30 BRASS, 0.8MM THK
 (0.8t JIS-3100C-2600P-1/2H)



- NOTES ;
1. PRODUCT SPEC No.108-5164
 2. APPLICATION SPEC No.114-5060,114-5052
 3. CUSTOMER MANUAL No ; CM-177J
 4. APPLIED CONTACT P/N ; 170032,170452,170454,170456
 5. WORKMANSHIP OF THE TAB HOLE EDGES MUST BE SUCH THAT EDGES MUST BE FREE FROM THE BURRS, WITH THE SHEAR DROOP NOT EXCEEDING 0.1 MILLIMETER
 6. CLEARANCE LINE FOR TAB TO MATE WITH COUNTERPART HOUSING
 7. GENERAL TOLERANCE :
 - x ≤ 10 : ±0.2
 - 10 < x ≤ 30 : ±0.25
 - 30 < x ≤ 100 : ±0.3
 - ANGLE : ±3°

66 NYLON	BLACK	172864-2
66 NYLON	WHITE	172864-1
MATERIAL	COLOR	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-		
		CHK	-		
DIMENSIONS: mm		APVD	-	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	-	250 SERIES AUTOMOTIVE POSITIVE DBL LOCK 2Pos COMBINATION HOUSING (T-TYPE)	
		APPLICATION SPEC	-	SIZE	A3
MATERIAL		WEIGHT	-	CAGE CODE	00779
		CUSTOMER DRAWING		DRAWING NO	172864
				RESTRICTED TO	-
				SCALE	1:1
				SHEET	1 of 1
				REV	E