



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16MAY2018	PV	HS

a) Part as supplied



b) Part after unrestricted recovery



DIMENSIONS

H		J		P	R	S	J0	HW	JW
Min a	Max b	Min a	Max b	±10%	±10%	±10%	±10%	±20%	±20%
21	11.3	11	6.3	105	15	12	88	1.5	1.1

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 2018 TE Connectivity Ltd.


DIMENSIONS: mm [INCHES]	DWN P. VU	16MAY2018	MATERIAL	SEE SHEET 2	FINISH	-
	CHK S. KURUP	16MAY2018	TE Connectivity Ltd.			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD H. SMITH	16MAY2018				
	0 PLC ± -	PRODUCT SPEC	NAME			
1 PLC ± -	APPLICATION SPEC	SIZE				A4
2 PLC ± -	WEIGHT	-	CAGE CODE	DRAWING NO		RESTRICTED TO
3 PLC ± -			A4 00779	G-222D211-X-G06-0		-
4 PLC ± -			CUSTOMER DRAWING			SCALE
ANGLES ± -			DNS			SHEET
			1 OF 2			REV
			A			

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	-	SEE SHEET 1	-	-

COMPATIBILITY CHART		
Material Dash No.	Material Description	SPEC No.
-3	Polyolefin, semi-rigid	RT-301
-4	Polyolefin, flexible	RT-1304
-12	Fluoroelastomer, flexible	RT-1312
-25	Elastomer, fluid-resistant	RW-2070
-100	Polyolefin, semi-flexible Zerohal	RT-1323 RW-2082

ORDERING INFORMATION

222D211-X-G06-0




RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT 2018 TE Connectivity Ltd.

THIS DRAWING IS UNPUBLISHED.

DIMENSIONS: mm [INCHES]	DWN P. VU	16MAY2018	MATERIAL SEE CHART	FINISH -		
	CHK S. KURUP	16MAY2018	 TE Connectivity Ltd.			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD H. SMITH	16MAY2018			NAME BOOT 90 DEG, 222D211-X-G06-0	
	PRODUCT SPEC -	APPLICATION SPEC -	SIZE A4	CAGE CODE 00779	DRAWING NO G-222D211-X-G06-0	RESTRICTED TO -
	WEIGHT -	CUSTOMER DRAWING		SCALE DNS	SHEET 2 of 2	REV A

