


REVISIONS				
REV	DESCRIPTION	DATE	BY	APP'D
H2	REVISED AS PER ECN-23-206271	23MAR2023	MT	GL



1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS (MEASURED DIFFERENTIALLY)

2 LABEL INFORMATION FOR 25 GIG PNS (-1 THRU -8): -1 SHOWN



3. SEE SHEET 2 FOR WIRING SCHEMATIC.

4. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.


5 TEST IN ACCORDANCE WITH IEEE802.3by.

6 DASH NUMBER 41 THRU 45 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

7 LABEL INFORMATION FOR 56 GIG PNS (-41 THRU -45): -41 SHOWN



8 CE MARKING LABEL INFORMATION (EXAMPLE SHOWS CHINA AND MEXICO MANUFACTURING ADDRESS):




DASH	WIRE GAGE	LENGTH	PART NO	
				STANDARD
6	26	3000 +80 -0	4-2821224-5	
	26	2500 +80 -0	4-2821224-4	
	26	2000 +80 -0	4-2821224-3	
	26	1500 +80 -0	4-2821224-2	
	26	1000 +50 -0	4-2821224-1	
5	26	5000 +80 -0	2821224-8	
	26	4000 +80 -0	2821224-7	
	26	3500 +80 -0	2821224-6	
	26	3000 +80 -0	2821224-5	
	26	2500 +80 -0	2821224-4	
	26	2000 +80 -0	2821224-3	
	26	1500 +80 -0	2821224-2	
	26	1000 +50 -0	2821224-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN T. SMITH 08OCT2015	TE Connectivity Ltd.
0. PLC ±	1. PLC ±	CHK C. POGASH 08OCT2015	
2. PLC ±	3. PLC ±	APP'D G. POGASH 08OCT2015	
4. PLC ±	ANGLES ±	NAME	CABLE ASSY, 26 AWG, SFP+ TO SFP+, 28GIG
MATERIAL	FINISH	APPLICATION SPEC	
		SIZE CAGE CODE DRAWING NO	RESTRICTED TO
		WEIGHT 0	A1 00779 C=2821224
		CUSTOMER DRAWING	SCALE 1:1 SHEET 1 OF 2 REV H2

REVISIONS				
REV	DATE	DESCRIPTION	BY	APP'D
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T.SMITH 08OCT2015		TE Connectivity Ltd.	
DIMENSIONS: mm		CHK C.POGASH 08OCT2015			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D C.POGASH 08OCT2015		NAME CABLE ASSY,26 AWG,SFP+ TO SFP+, 28GIG	
0. PLC ± -		PRODUCT SPEC		APPLICATION SPEC	
1. PLC ± -		SIZE A1		CAGE CODE 00779	
2. PLC ± -		DRAWING NO C=2821224		RESTRICTED TO	
3. PLC ± -		WEIGHT		SCALE 1:1	
4. PLC ± -		CUSTOMER DRAWING		SHEET 2 OF 2	
ANGLES ± -		FINISH		REV H2	