









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	24JAN2022	S.D	W.Z
	A1	RIVISE	12JAN2023	S.D	W.Z
	A2	ECR-24-2113B1	03JUL2024	SDT	W.Z



TBD-3	1.0-1.5	1.9-2.4	CuSn4	CuSn0.15/0.20	TIN		A = 3.0	E = 2.6	H = 4.4	16.8	SINGLE WIRE SEALING SYSTEM 	
-							B = 2.0	G = 2.9	K = 4.3			
TBD-1						TIN	C = 6.8	D _{br} = 1.35	D _{iso} = 2.9			M = 0.8
2438919-3	0.5-0.75	1.4-1.9	CuSn4	CuSn0.15/0.20	TIN		A = 2.6	E = 2.0	H = 4.2	16.3		
-							B = 2.0	G = 2.1	K = 4.3			
2438919-1						TIN	C = 6.4	D _{br} = 1.1	D _{iso} = 2.7			M = 0.8
2438918-3	0.25-0.35	1.1-1.6	CuSn4	CuSn0.15/0.20	TIN		A = 2.6	E = 1.8	H = 4.2	16.3		
-							B = 2.0	G = 1.8	K = 4.3			
2438918-1						TIN	C = 6.4	D _{br} = 0.8	D _{iso} = 2.6			M = 0.8
TBD-3	1.0-1.5	1.9-2.4	CuSn4	CuSn0.15/0.20	TIN		A = 3.0	E = 2.6	H = 3.7	16.3		FLR CABLE 
TBD-2							B = 2.0	G = 2.9	K = 3.9			
TBD-1						TIN	C = 6.1	D _{br} = 1.35	D _{iso} = 2.1			
2438914-3	0.5-0.75	1.4-1.9	CuSn0.15/0.20	CuSn0.15/0.20	TIN		A = 3.0	E = 2.0	H = 2.7	16.3		
2438914-2							B = 2.0	G = 2.1	K = 2.9			
2438914-1						TIN	C = 6.1	D _{br} = 1.1	D _{iso} = 1.6		M = 0.2	
2438913-3	0.25-0.35	1.1-1.6	CuSn0.15/0.20	CuSn0.15/0.20	TIN		A = 2.6	E = 1.8	H = 2.6	15.3		
2438913-2							B = 2.0	G = 1.8	K = 2.6			
2438913-1						TIN	C = 5.7	D _{br} = 0.8	D _{iso} = 1.4		M = 0.2	
ORDER NO. STRIP	WIRE RANGE (mm ²)	INSULATION-Ø (mm)	BODY	TAB	BODY	TAB	LENGTH	WIRE CRIMP	INSULATION CRIMP	DIMENSION MASS "L" (mm)	INSULATION CRIMP FOR	
			MATERIAL		SURFACE		CRIMP DIMENSIONS (mm)					

NOTE-

- 1 LASER WELDED
- 2 REVISION STATUS
- 3 CONTACT AREA TAB MIN. 0.8um SELECTIV GOLD OVER Ni
- 4 CONTACT AREA TAB MIN 2.0um SELECTIV SILVER
- 5 RETENTION FORCE INSERT TAB PUSHED INSIDE BODY MIN. 40N
- 6 DIFFERENT FORM OF THE SERRATIONS AND WIRE-CRIMP POSSIBLE
- 7 SEE APPLICATION SPECIFICATION TE-SPEC. 114-18464



PRODUCT CHARACTERISTICS AXL DMP_EMEA_012 BESONDERE MERKMALE NACH DMP_EMEA_012		TOLERANCING ISO 8015 TOLERIERUNG ISO 8015		DWG 24NOV2022 S.DU CHK 24NOV2022 LGU APVD W.ZHANG 24NOV2022 PRODUCT SPEC 108-10782 APPLICATION SPEC 114-10464		 TE Connectivity	
THIS DRAWING IS A CONTROLLED DOCUMENT.				NAME MCON 1.2 TAB-CB-TERMINAL -			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±°		SIZE A 00779		CASE CODE C=2438914	
MATERIAL -		FINISH -		DRAWING NO -		RESTRICTED TO -	
WEIGHT -				SCALE 10:1		SHEET 1 OF 1	
CUSTOMER DRAWING				REV A2			