D

С

В

\_\_\_\_

А


4

Ρ	LTR		
	А	INITIAL	RELEASE

SAFETY ORGANIZATIONS	
THIS FILTER WILL BE FORMALLY R	E (
THE LISTED AGENCY. THEREFORE,	ΑL
LATEST REVISION OF THE FOLLOWI	NC


UL APPROVED	50A 4
CSA RECOGNISED	50A 4

	2							
			REVISIONS					
	-	P LTR	DESCRIPTION	DATE	DWN	APVD		
		А	INITIAL RELEASE	30MAR2021	SR	СВ		
							D	
SIDE	THE LISTED A	WILL BE GENCY.	<u>IS</u> FORMALLY RECOGNIZED, CERTIFIED THEREFORE, ALL TEST/REQURIEMENT THE FOLLOWING AGENCY STANDARDS I	S SPECIFIED	ΙΝ Τ	ΗE		
	UL APPROVED CSA RECOGNIS	ЕD	50A 440V 50Hz/60Hz 40°C 50A 440V 50Hz/60Hz 40°C					
	<u>operating sp</u>	<u>ECIFICA</u> /VOLTAG	GE: 50A, 440VAC					
	MAXIMUM LEAK	AGE CUF	RRENT: 5mA @ 230VAC, 50Hz					
	OPERATING AM	BIENT T	EMPERATURE RANGE @ RATED CURREN	T: -25°C TO	+40°(	, ,		
		Τ, Τα,	HIGHER THAN 40°C, THE MAXIMUM OF				С	
	STORAGE TEMP	<u>RELIABILITY SPECIFICATIONS</u> STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C AND 95% RH						
		TEST SPECIFICATIONS INDUCTANCE, NOMINAL: 0.25mH						
	CAPACITANCE LINE TO GROU LINE TO LINE	ND, NOM						
_ TO TE ING SPECIFICATIO	N/G I.R. XXX	KΩ 1W Σ 1W	ISISTOR) 20°C, 50% RH AND 100VDC,	min: 6mΩ				
	LINE TO GROU	ND FOR	<u>NG INSPECITON HIPOT</u> 1 MINUTE: 2632VDC MINUTE: 1892VDC				В	
		TO SEL	ECT AND QUALIFY A FILTER IS FOR THE UNIT IN YOUR EQUIPMENT.	YOUR				
THIS DRAWING IS A CO	NTROLLED DOCUMENT DWN	30M	AR2021					
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED: APVD	E <u>ETH R</u> 30M <u>S BOLLE</u> 30M	AR2021 AR2021 NAME	TE Connectivi	t y			
	PLC ±- PRODUCT PRODUCT S   PLC ±0.5 -	SPEC	POWER LINE FILTER FO DIN 35 RAIL INSTALL 50KEBS6AFPDHM				А	
A	PLC ±0.0500 - NGLES ± INISH WEIGHT	- Er drawi	$A = \begin{bmatrix} c \text{ AGE CODE} \\ 0 & 0 & 7 & 7 \\ 0 & 0 & 7 & 7 \\ 0 & 0 & 7 & 7 \\ 0 & 0 & 0 & 7 \\ 0 & 0 & 0 & 7 \\ 0 & 0 & 0 & 0 \\ 0 & 0 & 0 & 0 \\ 0 & 0 &$	SHEET OF	RESTRIC			
	- CUSIOM	LN VRAWI		2 1	2	А	l	




TYPICAL INSERTION LOSS COMMON MODE 50/50 $\Omega$ ; DIFFERENTIAL MODE 50/50 $\Omega$ 

MH z	0.01	0.05	0.15	0.5	1	3	5	10	30
СМ	3	3	10	23	32	34	45	43	30
DM	3	4	8	29	31	36	42	49	49



470-19 (3/13)



А

DESCRIPTION DATE DWN APVD	REVISIONS			
	DESCRIPTION	DATE	DWN	APVD

С

В

=7	TE Connecti	v i t y	
ER LINE FI 35 RAIL I EBS6AFPDHM	NSTALLATION		А
GE CODE DRAWING NO	)	RESTRICTED TO	
)779 <b>C</b> =3-	1609965-9	-	
	SCALE 1:2 SHEET 2	of 2 Rev A	