



D

С


В

А

4

LINE SIDE

3



SAFETY ORGANIZATIONS

THIS FILTER WILL BE FORMALLY RECO THE LISTED AGENCY. THEREFORE, ALL LATEST REVISION OF THE FOLLOWING

UL APPROVED CSA APPROVED

#### OPERATING SPECIFICATION

LINE CURRENT/VOLTAGE: 50A, 440VAC LINE FREQUENCY: 50/60Hz

MAXIMUM LEAKAGE CURRENT: 5mA @ 23

OPERATING AMBIENT TEMPERATURE RAN

IN AN AMBIENT, Ta, HIGHER THAN 40° CURRENT,Io, IS AS FOLLOWS: Io=Ir

# RELIABILITY SPECIFICATIONS STORAGE TEMPERATURE: -40°C TO +85° HUMIDITY: 21 DAYS @ 40°C AND 95% F

TEST SPECIFICATIONS INDUCTANCE, NOMINAL: 0.25mH

CAPACITANCE @ 1kHz NEUTRAL TO GROUND, NOMINAL: 22nF LINE TO NEUTRAL, NOMINAL: 470nF

## DISCHARGE RESISTOR

 $L/G I.R. 2M\Omega$  1W L/L I.R.  $2M\Omega$ 1 W L/N I.R.  $1M\Omega$ 1 W N/G I.R. 680 K $\Omega$  1W IR (NO DISCHARGE RESISTOR) 20°C,

#### RECOMMENDED RECEIVING INSPECITON LINE TO GROUND FOR 1 MINUTE: 2632 LINE TO LINE FOR 1 MINUTE: 1892VD

LINE TO NEUTRAL FOR 1 MINUTE: 109

### FILTER APPROVAL


THE BEST WAY TO SELECT AND QUALIF ENGINEERING TO TEST THE UNIT IN Y

| THIS DRAWING IS A C | ONTROLLED DOCUMENT.   | DWN 14APR2021<br>SUPREETH R                    | _          |
|---------------------|---|--|------------|
| DIMENSIONS:         | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:   | CHK 14APR2021<br>CHRIS BOLLE<br>APVD 14APR2021 | NAME       |
| mm                  |   | CHRIS BOLLE                                    | l POWI     |
|                     | 0 PLC ±-<br>1 PLC ±0.5<br>2 PLC ±0.40<br>3 PLC ±0.130<br>4 PLC ±0.0500<br>ANGLES ±- | PRODUCT SPEC<br>-<br>APPLICATION SPEC<br>-     | DIN<br>50K |
| MATERIAL -          | FINISH -  | WEIGHT _                                       | A 3 0 c    |
| -                   | -   | CUSTOMER DRAWING                               |            |

L1 ⊶ ⊸ L1′ Ş L 2 ⊸ L2′ 0- $\leq$ L 3 ⊸ L3′ LOAD SIDE ş  $\top$ Ν Ν Ε E  $\left(\begin{array}{c} 1\\ \hline \end{array}\right)$  $\left(\begin{array}{c} 1\\ \hline \end{array}\right)$ SCHEMATIC

TYPICAL INSERTION LOSS COMMON MODE 50/50 $\Omega$ ; DIFFERENTIAL MODE 50/50 $\Omega$ 

| MH z | 0.01 | 0.05 | 0.15 | 0.5 | 1  | 3  | 5 10 |    | 30 |  |
|------|------|------|------|-----|----|----|------|----|----|--|
| СМ   | 4    | 4    | 11   | 24  | 32 | 42 | 48   | 34 | 20 |  |
| DM   | 14   | 20   | 28   | 42  | 50 | 30 | 26   | 20 | 22 |  |



| REVISIONS   |                     | DWA        |            |   |
|---|---------------------|------------|------------|---|
| description<br>ASE                                    | DATE<br>14APR2021   | dwn<br>S R | apvd<br>CB |   |
|   | 144572021           | <u>э</u> л |            |   |
|   |                     |            |            | D |
|   |                     |            |            |   |
| OGNIZED, CERTIFIED OR APP                             | PROVED F            | ιv         |            |   |
| L TEST/REQURIEMENTS SPECT<br>AGENCY STANDARDS WILL BE | IFIED IN            | , THE      |            |   |
| 50A 440V 50Hz/60Hz 40'                                |                     |            |            |   |
| 50A 440V 50Hz/60Hz 40'                                | с                   |            |            |   |
| C   |                     |            |            |   |
| 30VAC, 50Hz   |                     |            |            |   |
| NGE @ RATED CURRENT: -25°                             | C TO +1             | ∩° ⊂       |            |   |
| 0°C, THE MAXIMUM OPERATIN                             |                     | 0 0        |            |   |
| $r - \sqrt{\frac{85 - Ta}{45}}$                       |                     |            |            |   |
| V -   |                     |            |            |   |
| 5°C<br>RH   |                     |            |            |   |
|   |                     |            |            |   |
|   |                     |            |            |   |
|   |                     |            |            |   |
|   |                     |            |            |   |
|   |                     |            |            |   |
| FOR DU AND 100VDC MIN.                                | CMO                 |            |            |   |
| 50% RH AND 100VDC, MIN:                               | O MIZ Z             |            |            | В |
| <u>HIPOT</u><br>2VDC<br>DC                            |                     |            |            |   |
| 93VDC   |                     |            |            |   |
| FY A FILTER IS FOR YOUR                               |                     |            |            |   |
| YOUR EQUIPMENT.                                       |                     |            |            |   |
|   |                     |            |            |   |
| <b>STE</b> TE CO                                      | nnectivit           | у          |            |   |
|   |                     |            |            |   |
| VER LINE FILTER FOR<br>N RAIL 35 INSTALLATIO          | Ν                   |            |            |   |
| (ESS6AFPWVM<br>cage code   drawing no                 |                     | RESTRIC    | TED TO     | A |
| 0779 C=6-1609966-1                                    |                     | -          | . 20 10    |   |
| SCALE 1:2 SHEE  | т 1 <sup>оғ</sup> 2 | RE         | ΎΑ         |   |
|   |                     |            |            |   |

|   | 4   | 3            |                   | 2  |                                 |               |          |   |                   |              |                 |   |
|---|---|--------------|-------------------|--|---------------------------------|---------------|----------|---|-------------------|--------------|-----------------|---|
|   | C 2021 TE Connectivity. All Rights Reserved.  |              | I                 |  |                                 |               |          | REVISIONS                                 |                   |              |                 |   |
|   | NOTE 1 GROUND CONNECTION:<br>FOR ELECTRICAL SAFETY AND FILTER PERFORMANCE               |              |                   |  | Р                               | LTR           |          | DESCRIPTION                               | DATE              | DWN          | APVD            |   |
|   | UNIT MUST HAVE A GOOD GROUND CONNECTION.<br>TORQUE OUTER TERMINAL /GROUND NUTS: 2.5-3Nm |              |                   |  |                                 |               | SEE SHE  | ET 1                                      |                   |              |                 |   |
| D | NOTE 2 INPUT OUTPUT CONNECTION TERMINAL   |              |                   |  |                                 |               |          |   |                   |              |                 | D |
|   | AWG SIZE: XXX   |              |                   |  |                                 |               |          |   |                   |              |                 |   |
|   | THREADED BOLT SIZE FOR TERMINAL: M6<br>THREADED BOLT SIZE FOR GROUND: M6                |              |                   |  |                                 |               |          |   |                   |              |                 |   |
|   | NOTE 3 SUPPLIED WITH DIN RAIL BRACKET.  |              |                   |  |                                 |               |          |   |                   |              |                 |   |
|   | NOTE 4 DRAWING SHOWS DIN RAIL FOR   |              |                   |  |                                 |               |          |   |                   | $\searrow$   |                 |   |
|   | REFERENCE ONLY.   |              |                   |  |                                 |               |          |   |                   |              | -               |   |
|   |   |              |                   |  |                                 |               |          |   |                   |              |                 |   |
|   |   |              | I                 |  |                                 |               |          |   |                   |              |                 |   |
|   |   | <            | -                 |  |                                 |               |          |   |                   |              |                 |   |
|   | 0   |              |                   | 0  |                                 |               |          |   |                   |              |                 |   |
|   |   |              |                   |  |                                 | $\sum$        |          |   |                   |              |                 |   |
|   |   |              |                   |  |                                 |               |          |   |                   | 2            |                 |   |
| С |   |              |                   |  |                                 |               |          |   |                   |              |                 | С |
|   |   |              |                   |  |                                 |               | Г        |   |                   |              |                 |   |
|   |   | 100          |                   |  |                                 |               | _        | $\prec$                                   |                   |              |                 |   |
|   |   |              |                   |  |                                 |               |          |   | REAR SIDE         |              |                 |   |
|   |   |              |                   |  |                                 |               | Г        |   |                   |              | _               |   |
|   |   |              |                   |  |                                 |               |          |   | $\frown$          |              |                 |   |
|   |   | <u></u>      |                   |  |                                 |               |          |   |                   |              |                 |   |
|   | 0   |              |                   | 0  |                                 | _             |          |   |                   |              |                 |   |
|   |   |              |                   |  |                                 |               |          |   | $\langle \rangle$ |              |                 |   |
|   |   |              |                   |  |                                 |               |          |   |                   |              |                 |   |
| В |   |              |                   |  |                                 |               |          |   |                   |              |                 | В |
|   |   |              |                   |  |                                 |               |          |   |                   |              |                 |   |
|   |   | fr           |                   |  |                                 |               |          |   |                   | $\square$    | >               |   |
|   |   |              |                   |  |                                 |               |          | le la |                   | $\mathbf{i}$ |                 |   |
|   |   |              |                   |  |                                 |               |          | E I                                       |                   |              |                 |   |
|   |   |              |                   |  |                                 |               |          | FI  | RONT SIDE         |              |                 |   |
|   | DIN RAIL BRACKET DIN  | 35 BRACKET   | THIS DRAWING IS A | CONTROLLED DOCUMENT.                         | dwn<br>SUPREET                  | IH R          | PR2021   |   |                   | • 1          |                 |   |
|   |   | I JJ DRACKET | DIMENSIONS:       |  | снк<br>  Chris e                | 14AP<br>3011F | PR2021   | -ETE                                      | TE Connectiv      | i t y        |                 |   |
|   |   |              | mm                |  | APVD<br>CHRIS E<br>PRODUCT SPEC | JULLE         | PR2021 N | POWER LINE FILLE                          | r for             |              |                 |   |
| A |   |              |                   | $1 PLC \pm 0.5$<br>$1 2 PLC \pm 0.40$        | -                               |               |          | DIN RAIL 35 INST<br>50KESS6AFPWVM         | ALLAIION          |              |                 | А |
|   |   |              | $ $ $\forall$     | ☐ 3 PLC ±0.130<br>4 PLC ±0.0500<br>ANGLES ±- | APPLICATION<br>-                | SPEC          | 5        | SIZE CAGE CODE DRAWING NO                 |                   | RESTRI       | CTED TO         |   |
|   |   |              | MATERIAL _        |  | WEIGHT                          | -             | /        | 4300779C=6-1609                           | 966-1             |              | -               |   |
|   |   |              | -                 |  | CUSTOMER                        | DRAWIN        | IG       | SCALE                                     | 1:2 SHEET 2 C     | F2 R         | <sup>ev</sup> A |   |
| I | 470-19 (3/13)   |              |                   |  |                                 |               |          |   |                   |              |                 |   |