


Technical Data:

Case Material:Cover	Vyncolit black
Base Plate	PA GF black
Switch Lever Material	PA GF red
Min.Insulation Resistance	100MΩ
Dielectric Withstanding Voltage	1050V-1min.
Max.Contact Drop During Resistive Load	150mV
Voltage	up to 32VDC
Duty Rating	500A
Overload	1500A-4min.
.....	2000A-1.5min.
.....	2500A-10sec.

Auxiliary Contacts:

Continous Current:	10A
Make and Brake:	24V L/R 5ms 10A
.....	24V L/R 20ms 6A
Sealing	IP 67/ IEC 529
Vibration	4G/ 50-2000Hz
Shock	6G/ 11ms
Weight.....	350g
Temperature Range	-40°C bis +85°C
Wire Section(at nominal Load Main Terminals) .	min. 250mm ²
Switch Lever	not removeable
Max. Torque (Main Terminals).....	18-22Nm

Circuit



Für diese Zeichnung behalten wir uns das Urheberrecht gemäß DIN 34 vor

Datum	Name	Freimaßtoleranz	Maßstab
Bearb. 15.10.2014	Mielk	DIN ISO 2768 cL	1:2
Gepr. 22.04.2016	Grind		



Zeichnungs-Nr.:

35-514-231-R-A5-903

Vers.Nr.: