




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		G3		REVISED PER ECR-17-018757	25APR2018	BDA	SG



1 MATERIAL: CONNECTOR-NYLON UL94V-0 (BLACK).  
 CONTACTS-0.30 [.012] THICK COPPER ALLOY  
 BRIGHT TIN-LEAD 0.00203 [.000080] MIN THICK FOR CONTACTS  
 644312-2 THRU 1-644312-5  
 MATTE WHISKER MITIGATED TIN PLATE 0.00203 [.000080] MIN THICK  
 OVER 0.00076 [.000030] MIN THICK NICKEL FOR CONTACTS  
 3-644312-2 THRU 4-644312-5

- 2. CONTACTS ACCEPT 24 AWG WIRE WITH 1.52 [.060] MAX INSULATION DIAMETER.
- 3. CONTACTS MUST ACCEPT 0.64±0.03 [.025±.001] SQUARE POST AND REMAIN LOCKED IN POSITION.
- 4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
- 5. DIMENSIONS IN BRACKETS ARE IN INCHES.

6. HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP AND WITH POLARIZING TAB.

- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 8 OBSOLETE PARTS

LEAD FREE	38.10 [1.500]	15	4-644312-5
	35.56 [1.400]	14	4-644312-4
	33.02 [1.300]	13	4-644312-3
	30.48 [1.200]	12	4-644312-2
	27.94 [1.100]	11	4-644312-1
	25.40 [1.000]	10	4-644312-0
	22.86 [.900]	9	3-644312-9
	20.32 [.800]	8	3-644312-8
	17.78 [.700]	7	3-644312-7
	15.24 [.600]	6	3-644312-6
	12.70 [.500]	5	3-644312-5
	10.16 [.400]	4	3-644312-4
	7.62 [.300]	3	3-644312-3
	5.08 [.200]	2	3-644312-2

CONTAINS LEAD	38.10 [1.500]	15	1-644312-5
	35.56 [1.400]	14	1-644312-4
	33.02 [1.300]	13	1-644312-3
	30.48 [1.200]	12	1-644312-2
	27.94 [1.100]	11	1-644312-1
	25.40 [1.000]	10	1-644312-0
	22.86 [.900]	9	644312-9
	20.32 [.800]	8	644312-8
	17.78 [.700]	7	644312-7
	15.24 [.600]	6	644312-6
	12.70 [.500]	5	644312-5
	10.16 [.400]	4	644312-4
	7.62 [.300]	3	644312-3
	5.08 [.200]	2	644312-2

DIM A	NO.OF POSN	ASSEMBLY
-------	------------	----------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 24-FEB-2004	<b>STE</b> TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 24-FEB-2004		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 24-FEB-2004	NAME MTA 100 CONNECTOR ASSEMBLY, 24 AWG, UL94V-0, SPECIAL	
0 PLC ±	1 PLC ±	PRODUCT SPEC 108-1050	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
2 PLC ± 0.13 [.005]	3 PLC ±	APPLICATION SPEC 114-1019	A2 00779 C=644312	
4 PLC ±	ANGLES ± 0°30'	FINISH	WEIGHT	SCALE 5:1 SHEET 1 OF 1 REV G3
MATERIAL			CUSTOMER DRAWING	