


REV. B
DCO-2020-09-02T11_56_41

COIL: @ 25°C	
RESISTANCE	700 OHMS ±0 %
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	13.5 VDC
	8.0 VDC MAX, 1.5 VDC MIN.
MUST RELEASE	

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	100 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES: OPERATE 4 MS MAX	
RELEASE 4 MS MAX	
CONTACT STABILIZATION TIME 2.5 MS MAX	
ALL OTHER REQUIREMENTS TO M39016/6-109M	

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	LOW LEVEL TO
	2 AMPS 28 VDC RESISTIVE 100,000
	OPERATIONS

DR. RB 19Nov1993 CK. JMB 19Nov1993



CUST. QPL
CUST. NO. M39016/6-109M REV.

TE NUMBER
2-1617031-1

CII PART NUMBER
HFW 1201K45M