

## Miniature PCB Relay OJS 10A/16A short pin

- 1 pole 10/16A, 1 form A (NO)
- 10A rating with sensitive coil 200mW
- Small size (18.2 x 10.2 x 14.8mm)
- 4000Vrms coil to contact dielectric strength
- Product in accordance to IEC 62368-1



Lihting, smart plug, power supply, appliances, industrial control.







Approvals		
Certification No.	TUV R50497672.	UL

L E82292, CQC21002289617

Technical data of approved types on request

Contact Data		
Contact arrangement	1 for	m A, 1 NO
Rated voltage	2	50VAC
Max. switching voltage	2	77VAC
Rated current	10A(H	M), 16A(HE)
Contact material	Ag	SnOlnO
Min. recommended contact load	100m	A at 5VDC
Frequency of operation with/without load	360/18	3000 ops./h
Operate/release time max. (including bounce	e time)	OJS-HM:15ms/4ms
		OJS-HE:10ms/4ms
Electrical endurance 1)		
UL, TUV, CQC		
HM, 10A, 250VAC, +85°C		50x10 <sup>3</sup> ops.
HE, 16A, 250VAC, +85°C		30x10 <sup>3</sup> ops.
Internal test		
8A, 250VAC res, +23°C		100x10 <sup>3</sup> ops.
Mechanical endurance, DC coil		10x10 <sup>6</sup> ops.

<sup>1)</sup> Consult with application engineers about contact performance of wash tight version.

Coil Data		
Coil voltage range	5 to 48VDC	
Operative range, IEC 61810	2	
Coil insulation system according UL	Class F	

Coil versions, DC coil, OJS-HM type

0011 1010	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	,	, po		
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	Ω±10%	mW
05	5	3.75	0.25	125	200
12	12	9	0.6	720	200
24	24	18	1.2	2880	200

Coil versions, DC coil, OJS-HE type

Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDČ	VDČ	VDČ	Ω±10%	mW
05	5	3.75	0.25	56	450
12	12	9	0.6	320	450
24	24	18	1.2	1280	450
48	48	36	2.4	5120	450

All figures are given for coil without pre-energization, at ambient temperature +23°C

Insulation Data	
Initial dielectric strength	
between open contacts	750V <sub>rms</sub>
between contact and co	il 4000V <sub>rms</sub>
Initial insulation resistance	1000ΜΩ
Clearance/creepage	
between contact and co	il 7mm / 11mm
Type of insulation	Reinforced insulation between coil and contacts

Oth	er	Data	

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.te.com/customersupport/rohssupportcenter

Ambient temperature -40°C to +85°C

Category of environmental protection IEC 61810 RTII - flux proof

RTIII - wash tight

Vibration resistance 10 to 55Hz, double amplitude 1.5mm Shock resistance (functional) 10g

Shock resistance (destructive) 100g 240h, -40°C Cold storage Dry heat 240h, +85°C Temperature cycling (Shock) 100cycles, -40/+85°C OJS-HM: 1,000hrs, 10A, +85°C Thermal endurance

OJS-HE: 1,000hrs, 16A, +85°C Weight Approx. 5.8g

Resistance to soldering heat THT


IEC 60068-2-20 RTII: 270°C/10s RTIII: 260°C/10s tray/100, Carton box/1000 Packaging unit





# Miniature PCB Relay OJS 10A/16A Short pin (Continued)

#### **Dimensions**


#### OJS HM 10A Outline and PCB Layout









### OJS HE 16A Outline and PCB Layout








### Terminal assignment

Bottom view on solder pins





# Miniature PCB Relay OJS 10A/16A Short pin (Continued)

	1		
			J

Product code	Rating	Enclosure	Coil voltage	Coil power	Insulation	Part number
OJS-SH-105HMF, 01000		Wash tight	5VDC			1-2071556-7
OJS-SH-112HMF, 01000			12VDC			1-2071556-3
OJS-SH-124HMF, 01000	104		24VDC	200mW		1-2071556-8
OJS-SS-105HMF, 01000	10A	Flux proof	5VDC	20011100		1-2071556-4
OJS-SS-112HMF, 01000			12VDC			1-2071556-5
OJS-SS-124HMF, 01000			24VDC		Class F	1-2071556-6
OJS-SH-105HEF, 01000			5VDC		Class F	2-2071556-2
OJS-SH-112HEF, 01000	1	Wash tight	12VDC			2-2071556-3
OJS-SH-124HEF, 01000	164		24VDC	450mW		2-2071556-4
OJS-SS-105HEF, 01000	16A		5VDC	43011100		1-2071556-9
OJS-SS-112HEF, 01000	1	Flux proof	12VDC			2-2071556-0
OJS-SS-124HEF, 01000	1		24VDC			2-2071556-1

Other types on request.

This list represents the most common types and does not show all variants covered by this data sheet.