

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P6		REVISED PER ECR-18-011787	10SEP2018	JB	DZ
P7		REVISED PER ECN-23-210752	05MAY2023	WLS	VS

4.06±0.10  
 1.98±0.20  
 8.71±0.20  
 7.11±0.10  
 DIM B ±0.10  
 DIM C ±0.05

PANEL CUT-OUT  $\triangle 9$

$\triangle 1$   
 $\triangle 5$

$\triangle 1$  CIRCUIT IDENTIFIERS LOCATED APPROXIMATELY AS SHOWN.  
 $\triangle 2$  MATERIAL PA66/6 UL94-V0.  
 $\triangle 3$  MATERIAL PA66 UL94-V0, GWEPT 750°C AND GWFI 850°C, NO FLAME ACC. TO IEC 60335-1.  
 $\triangle 4$  MATERIAL ID ">PA<" LOCATED IN APPROX AREA SHOWN, APPROX 0.01 HIGH.  
 $\triangle 5$  CAVITY NUMBER IDENTIFICATION.  
 6 COUNTERPART RECOMMENDED IS PN 794617 (DASH ACC. TO NUMBER OF POSITION).  
 7 TERMINAL USED WITH THIS CONNECTOR CAN BE 794608 OR 794609 OR LOOSE PIECE TERMINALS MAKE FROM THEM OR OTHER APPROVED BY PRODUCT ENGINEERING (TERMINAL PN DEFINED ACC. TO WIRE SIZE AND DASH NUMBER ACC. TO FINISHING).  
 8 PANEL MUST BE PUNCHED SO THAT HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.  
 $\triangle 9$  RECOMMENDED PANEL THICKNESS 1.57-2.3.

3.00 REF  
 3.00  
 DIM A

6.86  
 8.50  
 16.89 REF

$\triangle 1$   
 $\triangle 4$













COLOR	MATERIAL	DIM C	DIM B	DIM A	NO. OF POS.	PART NUMBER
NATURAL	$\triangle 3$	19.88	16.20	15.85	10	3-794615-0
		16.88	13.20	12.85	8	3-794615-8
		13.88	10.20	9.85	6	3-794615-6
BLACK	$\triangle 2$	40.88	37.20	36.85	24	2-794615-4
		37.88	34.20	33.85	22	2-794615-2
		34.88	31.20	30.85	20	2-794615-0
		31.88	28.20	27.85	18	1-794615-8
		28.88	25.20	24.85	16	1-794615-6
		25.88	22.20	21.85	14	1-794615-4
		22.88	19.20	18.85	12	1-794615-2
		19.88	16.20	15.85	10	1-794615-0
		16.88	13.20	12.85	8	794615-8
		13.88	10.20	9.85	6	794615-6
		10.88	7.20	6.85	4	794615-4
		7.88	4.20	3.85	2	794615-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W J RUDY 29AUG2000	TE Connectivity NAME PLUG HOUSING, 2 to 24 POSITION DUAL ROW, PANEL MOUNT MICRO MATE-N-LOK(TM)					
DIMENSIONS: mm		CHK W DAVIS 29AUG2000				SIZE 108-1836	CAGE CODE A200779	DRAWING NO C-794615
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W DAVIS 29AUG2000				APPLICATION SPEC 114-13000	RESTRICTED TO	
0 PLC ± 1 PLC ± 2 PLC ±0.26 3 PLC ± 4 PLC ± ANGLES ±1° FINISH -		PRODUCT SPEC 108-1836				WEIGHT -	SCALE 4:1	SHEET 1 OF 2
MATERIAL SEE TABLE		CUSTOMER DRAWING		REV P7				

1471-9 (3/13)

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



KEYING BY POSITION SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W J RUDY 29AUG2000	TE Connectivity		
DIMENSIONS: mm		CHK W DAVIS 29AUG2000			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W DAVIS 29AUG2000	NAME PLUG HOUSING, 2 to 24 POSITION DUAL ROW, PANEL MOUNT MICRO MATE-N-LOK(TM)		
0 PLC ±-		PRODUCT SPEC	SIZE		
1 PLC ±-		108-1836	CAGE CODE		
2 PLC ±0.26		APPLICATION SPEC	DRAWING NO		
3 PLC ±-		114-13000	RESTRICTED TO		
4 PLC ±-		WEIGHT	A200779C-794615		
ANGLES ±°		CUSTOMER DRAWING	SCALE	SHEET	REV
FINISH		4:1	2	2	P7