


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	PART OBSOLESCENCE	26MAR2024	KA	SS

NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄBLICH

POS. PER ROW	L±0.4	PART NUMBER		
-	-	-	-	-
2	5.08	828221	-2	OBSOLETE
3	7.62		-3	△
4	10.16		-4	
5	12.70		-5	OBSOLETE
6	15.24		-6	OBSOLETE
7	17.78		-7	
8	20.32		-8	OBSOLETE
9	22.86		-9	OBSOLETE
10	25.40		-0	OBSOLETE
11	27.94	1-	-1	
12	30.48	1-	-2	OBSOLETE
13	33.02	1-	-3	△
14	35.56	1-	-4	OBSOLETE
15	38.10	1-	-5	△
16	40.64	1-	-6	△
17	43.18	1-	-7	OBSOLETE
18	45.72	1-	-8	△
19	48.26	1-	-9	
20	50.80	2-	-0	△
21	53.34	2-	-1	△
22	55.88	2-	-2	△
23	58.42	2-	-3	△
24	60.96	2-	-4	△
25	63.50	2-	-5	
26	66.04	2-	-6	
27	68.58	2-	-7	
28	71.12	2-	-8	
29	73.66	2-	-9	
30	76.20	3-	-0	
31	78.74	3-	-1	
32	81.28	3-	-2	
33	83.82	3-	-3	
34	86.36	3-	-4	
35	88.90	3-	-5	
36	91.44	3-	-6	
37	93.98	3-	-7	
38	96.52	3-	-8	
39	99.06	3-	-9	
40	101.60	4-	-0	
41	104.14	4-	-1	
42	106.68	4-	-2	
43	109.22	4-	-3	
44	111.76	4-	-4	
45	114.30	4-	-5	
46	116.84	4-	-6	
47	119.38	4-	-7	
48	121.92	4-	-8	
49	124.46	4-	-9	
50	127.00	5- 828221	-0	OBSOLETE



- 1 MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au OVER Min 1.27µm Ni)
SOLDER SIDE : MIN. 2.5µm TIN OVER Min 1.27µm NICKEL
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

CONTACT PIN	CuZn	△
PIN HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	COLOR FINISH

TE Connectivity. All Rights Reserved. © 2023

DIMENSIONS: mm	DWN	20FEB1985	MATERIAL	SEE TABLE	FINISH	SEE TABLE	
	CHK	22FEB1985	TE TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	M.SCHAARSCHMIDT						NAME
±0.2 mm	PRODUCT SPEC	108-18012		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -	APPLICATION SPEC	-		A4	00779	828221	-
1 PLC ± -	WEIGHT	-		CUSTOMER DRAWING			SCALE
2 PLC ± -							4:1
3 PLC ± -							SHEET
4 PLC ± -							1 OF 1
ANGLES ± -							REV
							C2

