

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	16APR2015	DW	CW
	B	ECR-15-018270	09DEC2015	DW	CW
	C	ECR-21-111798	27SEP2021	WQR	CW



NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 830V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
WIRE RANGE: $0.14\sim 4\text{ mm}^2$ (26~12 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20300X20XX000)

注释:

- 技术参数:
绝缘材料: PC
额定电压: 830V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40\sim+125^{\circ}C$
接线范围: $0.14\sim 4\text{ mm}^2$ (26~12 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20300X20XX000)

HMN-006-PF	T2111063201-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	16APR2015	 TE Connectivity	
DIMENSIONS:		CHK	16APR2015		
mm		APVD	16APR2015		
		PRODUCT SPEC	108-137120		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	HMN-006-PF		RESTRICTED TO
0 PLC \pm		APPLICATION SPEC	114-137120		
1 PLC \pm		WEIGHT	-		-
2 PLC \pm		SIZE	A3	00779	
3 PLC \pm		DRAWING NO		T2111063201000	
4 PLC \pm		SCALE		3:2	SHEET 1 OF 1
ANGLES \pm		REV		C	
FINISH		Customer Drawing			

1470-19 (3/13)