



## 3/4" 90 Degree Angle, Mirror Mount L-Bracket

LBM9034 - LBMB9034-L

### 3/4", MOBILE MOUNT BRACKETS, 90 DEGREE ANGLE, MIRROR L-BRACKETS

Our aluminum mirror mount brackets are extruded and not stamped. This results in a stronger more durable bracket without the risk of bend fatigue and cracking that may occur with inferior stamped aluminum products. Aluminum mirror mounts are bright or black anodized for corrosion protection.

#### FEATURES

- Bright or black anodized corrosion protection.
- Brackets are extruded not stamped providing high durability.

#### MARKETS

- Land Mobile Radio
- Public Safety, Commercial & Industrial


#### SPECIFICATIONS

|                       |                          |
|-----------------------|--------------------------|
| Hole Size             | 3/4"                     |
| Mast Mounting Dia     | Min - 11mm<br>Max - 22mm |
| Finish                | Bright or Black          |
| Dimensions            | 90 degree angle          |
| Type                  | Mirror L-bracket         |
| Depth                 | 1.9"                     |
| Width                 | 2"                       |
| Height                | 0.4 lb                   |
| Weight                | 13 x 14.7 x .25 cm       |
| Manufacturing Process | Extrusion                |

#### PART CONFIGURATION

|            |        |
|------------|--------|
| LBM9034    | Bright |
| LBMB9034-L | Black  |

# MECHANICAL DRAWINGS



## TE TECHNICAL SUPPORT CENTER

- USA: +1 (800) 522-6752
- Canada: +1 (905) 475-6222
- Mexico: +52 (0) 55-1106-0800
- Latin/S. America: +54 (0) 11-4733-2200
- Germany: +49 (0) 6251-133-1999
- UK: +44 (0) 800-267666
- France: +33 (0) 1-3420-8686
- Netherlands: +31 (0) 73-6246-999
- China: +86 (0) 400-820-6015

## te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original