



Mesh Series™

Omni Antennas ODxxM

2.4-5.85 GHz VERTICALLY POLARIZED OMNIDIRECTIONAL ANTENNA

The Mesh Series™ omnidirectional antenna series are designed with mesh networking in mind. With their waterproof N male connector they can be easily mounted to an enclosure like the die-cast enclosure (DCE-7x6x2) to give total wireless coverage. Various gains and frequencies are available. They are constructed of UV resistant materials and are waterproof for a long service life.

FEATURES

- Mesh networking vertically polarized omni-directionals
- Various gains available: 5dBi to 12dBi
- Various frequencies available: 2.4GHz & 5GHz
- Type N male integrated connector
- Rugged, lightweight, and waterproof

MARKETS


- Mesh networking applications
- 2 to 6 GHz wireless applications
- Point to multi-point systems
- Base station antennas
- Wi-Fi access points
- WiMax base stations

PARAMETER


VSWR	1.5:1
Impedance	50 ohm
Input power	10W
Rate wind velocity	125 mph (56 m/sec)
Operating temperature	-40 - +70°C
IP Rating	IP53

MODEL	FREQ. (MHz)	GAIN	VERT BW	WEIGHT	DIM (L X DIA)
OD24M-5	2400-2485	5dBi	25°	0.5 lbs (0.2 kg)	12 x 0.6 in (355 x 15 mm)
OD24M-9	2400-2485	9dBi	14°	0.8 lbs (0.4 kg)	27 x 0.6 in (690 x 15 mm)
OD58M-12	5400-5850	12dBi	7°	0.65 lbs (0.5 kg)	27.5 x 0.6 in (700 x 15 mm)


ANTENNA PATTERNS



OD24M-5 E-Plane



OD24M-9 E-Plane



OD58M-12

SYSTEM ORDERING

OD -- M- --

Frequency

24 = 2400 to 2485 MHz
 35 = 3400 to 3600 MHz
 49 = 4940 to 4990 MHz
 58 = 5400 to 5858 MHz
 5W = 5150 to 5850 MHz

Gain

5 = 5dBi
 12 = 12dBi

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable.

However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

©2023 TE Connectivity. All Rights Reserved.

12/23 Original

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015