



626 PNEUMATIC TOOL SYSTEM

The Effortless Alternative to Hand Crimping

626 PNEUMATIC TOOL SYSTEM

FAST FACTS

Effortless crimping for a broad range of terminals, either bench-mounted or hand-held for working in cramped quarters.

- Lightweight tool eliminates physical force required by hand tools
- Hand- or foot- switch operation
- Termination wire range from 26-6 AWG [0.12-13.0mm²], plus coaxial and fiber optic cable
- Works with existing TE-compatible crimp heads and die sets
- Ratchet control option provides complete crimp cycle, eliminating partial crimps
- Use rotating head assembly to reach difficult termination locations
- Engineered and manufactured using processes independently certified to internationally recognized quality standards ISO-9001:2000 and telecommunications Industry Standard TL 9000

626 Pneumatic Tool System

Maximize your productivity while minimizing your effort—replace your manual hand tools with the 626 Pneumatic Tool System. Terminating wires from 26-6 AWG [0.12-13.0 mm²] has never been easier. And you can continue to use most, if not all, of your existing AMP-compatible crimp heads and die sets.

Stop Working So Hard

The powerful 626 Pneumatic Tool System makes crimping as easy as pressing a hand or foot switch. Besides reducing operator fatigue, this means you don't have to design your production bench around your tool. Include the fully adjustable Bench Mount Assembly with the foot switch, and you're completely free to concentrate on aligning the wire and terminal. Now you can crimp faster and with fewer mistakes.



The 626 System Works Where and How You Need It

Using 626 adapters, tools previously restricted to prototype or limited production applications can now be used in low to medium bench production and harness assembly operations. Because the 626 crimp head can be rotated to any angle, you can also work on those difficult terminations in confined equipment cabinets or enclosures.

Looking for the complete crimp cycle control provided by the mechanical ratchet in premium CERTI-CRIMP hand tools? The available 626 System ratchet tool holders produce a complete crimp cycle by simply pressing a switch. Dies will fully bottom before you can open the jaws to release the crimped product.

Protect Your Investment

The 626 System's power unit works with a variety of adapters and tool holders, so you can continue to work with your existing crimp heads and die sets.

tooling.te.com

626 PNEUMATIC TOOL SYSTEM

626 Pneumatic System Power Unit



Outside Diameter	45 mm [1.8]
Length	225 mm [8.88] for foot actuated unit
Grip Span	55mm [2.19] over button/handle
Mass	0.60 kg [1.32 lbm] for foot actuated unit
Air Pressure	6.21-6.89 bar [90-100 psi]
Air Displacement	0.00018 m ³ [11.14 in ³]
Air Supply Hose	3.05 m [10 ft] long, 4.8 mm [3/16] I.D.
Cycle Time	0.7-0.8 s (for 16-14 AWG [1.3-2 mm ²])

Big Return in a Micro Package

Does your crimping application demand even more accessibility and flexibility than the 626 System offers? The Micro Pneumatic Tool System terminates wires in the 26-14 AWG [0.12-2 mm²] range,* but with a smaller and lighter power unit. Weighing in at only 0.7 kg [1.5 lb] and just 146.5 mm [5.75 in] long, the hand-actuated Micro System is compatible with three different head systems.

* With the exception of the SOLISTRAND head combination which crimps 22-10 AWG [0.3-2 mm²] combinations.

Micro Pneumatic System Power Unit

Outside Diameter	45 mm [1.8]
Length	146.5 mm [5.75]
Grip Span	55mm [2.19] over button/handle
Mass	0.70 kg [1.5 lbm]
Air Pressure	6.21-6.89 bar [90-100 psi]
Air Displacement	0.00018 m ³ [11.14 in ³]
Air Supply Hose	3.05 m [10 ft] long, 4.8 mm [3/16] I.D. with 1/8 in NPT fitting
Cycle Time	0.7-0.8 s (for 16-14 AWG [1.3-2 mm ²] PIDG Terminals)



Die Interchangeability

For the ability to change dies quickly when needs change, whether from one terminal type to another or from tool to tool when workload and environment change, consider the SDE family of tools and dies. For more information, see Catalog 1773379-1.

SDE Compatible Kit

Complete tool with hand-held power unit	P/N 1213855-1	0.3 - 6.0mm ² (22-10 AWG)
---	---------------	--------------------------------------



Tool and Adapter Holders*

	Large Tool Holder	Small Tool Holder	Adapter Holder
Length (with Head Assembly)	100 [3.88]	70 [2.75]	70 [2.75]
Weight (with Head Assembly)	0.76 kg [1.68 lb]	0.44 kg [0.96 lb]	0.44 kg [0.96 lb]

*Measurements are averages.

Bench Mount Assembly*

Base Size	200 x 200 [8 x 8]
Weight	2.9 kg [6.5 lb]
Bench Mounting Dimensions	Base has two, 1/4-20 tapped holes on 150 [6] centerlines
Part. No	856402-1

*Not for use in the European Community.


tooling.te.com

626 PNEUMATIC TOOL SYSTEMS

System Configurations and Ordering Information

626 Pneumatic Tool System

A basic 626 Pneumatic Tool System requires a power unit, a tool holder, a head assembly, and a die set, when applicable. Tool holder assemblies (i.e., tool holder and cam) accept the crimping heads, adapters, and die sets listed on pages 6 through 7.



¹ 3.05 m [10 ft] Air Supply Hose (Part No. 38111) included with each power unit.


² A mark adjacent to a crimping head or adapter indicates it conforms to European Union Directives in handheld applications.

626 PNEUMATIC TOOL SYSTEM

System Configurations and Ordering Information

Micro Pneumatic Tool System

A basic Micro Pneumatic Tool System requires a power unit, a tool holder, a head assembly, and a die set, when applicable. Tool holder assemblies (i.e., tool holder and cam) accept the crimping heads, adapters, and die sets listed on pages 7 and 8.



Note: A CE mark adjacent to a crimping head or adapter indicates it conforms to European Union Directives in hand-held applications.

626 PNEUMATIC TOOL SYSTEM

626 System Crimping Heads and Die Sets



Crimping Heads for Large Tool Holders

626 SYSTEM CRIMPING HEADS AND DIE SETS

Wire Size Range	Wire Size Range		Crimping Head Part Number	Instruction Sheet Number	Die Set Part Number
	AWG	mm ²			
PIDG FASTON Receptacles (P/N Series 6409 Only)	22-18	0.3-0.9	679305-1 [†] (TETRA-CRIMP)	408-4099	—
	16-14	1.3-2			
	12-10	3-6			
PIDG Terminals and Splices, PLASTI-GRIP Terminals	22-16	0.3-1.3	679300-1	408-4071	—
	16-14	1.3-2			
	12-10	3-6			
PIDG Terminals and Splices, PLASTI-GRIP Terminals	16-14 HD, 12-10	1.3-2 HD, 3-6	679300-1	408-4071	—
PLASTI-STRIP Terminals, Ultra-Fast Plus FASTON Receptacles	22-18	0.3-0.9	679992-1 ^{††}	408-4098	58079-3
	16-14	1.3-2			58080-3
Ultra-Fast FASTON Tabs and Receptacles	22-18	0.3-0.9	679301-1	408-4072	90390-3
	16-14	1.3-2			1338758-1
SOLISTRAND Uninsulated Terminals and Splices	22-10	0.3-6	679304-1	408-4070	Request Catalog 82276 for a listing of over 75 die sets.
	8	8	189896-1		
	6	13	189466-1		
Adapter for PRO-CRIMPER III Die Sets	—	—	679304-1	408-4070	—
	ECV 18-8	0.9-8	189896-1	408-4111	—
Closed End Splices (Insulated)	CES 18-10	0.9-6	189466-1	408-4175	—
	STRATO-THERM Terminals and Splices	22-10	0.3-6	217206-1	408-4110
COPALUM Terminals and Splices	16-14	1.3-2	189447-1	408-9989	—
	12-10	3-6	189444-1		
	8	8	1320169-1		
TERMINYL Terminals	8	8	904395-1	408-4451	—
TERMI-FOIL Barrel Terminals, Strip Tap Terminals and Splices	8	8	217923-1	408-4171	305956-3 (0.016 [0.40] Max. Foil Thk.)
					305956-3 (0.016 [0.70] Max. Foil Thk.)

[†] Equivalent to TETRA-CRIMP Hand Tool Part No. 59824-1; die set is NOT interchangeable.

^{††} Uses same die as Platform Die Hand Tool Part No. 58078-3.

Requires Hand Actuated Power Unit Part No. 189721-2 or Foot Actuated Power Unit Part No. 189722-2.

tooling.te.com

626 System Crimping Heads and Die Sets



Crimping Heads for Small Tool Holders

Crimping Heads and Die Sets for Small Tool Holders

Products Applied	Wire Size Range		Crimping Head Part Number	Instruction Sheet Number
	AWG	mm ²		
PIDG Terminals and Splices and PLASTI-GRIP Terminals	22-16	0.3-1.3	314270-3	408-9586
	16-14	1.3-2	314269-1	
SOLISTRAND Uninsulated Terminals and Splices	22-10	0.3-6	189989-1	408-9585

Micro Pneumatic Crimping Heads

Double Action Crimping Heads

Products Applied	Wire Size Range		Crimping Head Part Number
	AWG	mm ²	
PIDG Terminals and Splices and PLASTI-GRIP Terminals	22-16	0.3-1.3	314270-3
	16-14	1.3-2	314269-1
SOLISTRAND Uninsulated Terminals and Splices	22-16	0.3-1.3	189989-1
	16-14	1.3-2	
	14-12	2-3	


T-HEAD Crimper

Products Applied	Wire Size Range		T-HEAD Assembly
	AWG	mm ²	
PIDG Terminals & Splices	22-16	0.3-1.25	2217485-1
PLASTI-GRIP Terminals	16-14	1.25-2	

T-HEAD Crimper

Part No. 217485-1

Used to apply 22-14 AWG [0.3-2 mm²] PIDG Terminals and Splices and PLASTI-GRIP Terminals. (Equivalent to T-HEAD Hand Tool Part Nos 59170 and 59250.)



tooling.te.com

626 PNEUMATIC TOOL SYSTEM

Micro System Crimping Heads

CERTI-CRIMP II, Straight Action (SAHT) Adapter Crimping Heads

Products Applied		Wire Size Range		SAHT	
Connector/Terminal	Style	AWG	mm ²	Tool Assembly*	Head Only
AMPLIMITE D-Sub. Connectors	Size 20 DF Contacts	28-24	0.08-0.2	91503-1	91503-1
		24-20	0.2-0.5		
	Size 22 DF Contacts	28-22	0.08-0.3	91520-1	91520-3
AMPMODU Connectors	Mod. IV Contacts	26-22	0.12-0.3	91517-1	91517-1
		24-20	0.2-0.5	91516-1	91516-3
	Locking Clip Contacts	26-22	0.12-0.3	91533-1	91533-1
		MTE & Tandem Spring Contacts	32-28	0.03-0.08	91543-1
	Short Point Contacts	26-22	0.12-0.3	91531-1	
		32-22	0.03-0.3	91518-1	
CPC Connectors M series Connectors	Type II Contacts	28-24	0.08-0.2	91539-1	91539-3
		24-20	0.2-0.5		
		18-14	0.8-2		
	Type III+ Contacts	26-24	0.12-0.2	91515-1	91515-3
		24-20	0.2-0.5	91523-1	91515-3
		24-20	0.2-0.5		
		18-16	0.8-1.25	91505-1	91505-3
		24-20	0.2-0.5		
		18-16	0.8-1.25		
		18-14	0.8-2	91519-1	91519-3
Commercial Contacts	30-22	0.05-0.3	91515-1	91515-3	
	24-18	0.2-0.8	91512-1	91512-3	
	20-14	0.5-2	91504-1	91504-3	
MATE-N-LOK Connectors	Universal & Universal II Contacts	24-18	0.2-0.8	91510-1	91510-1
		20-14	0.5-2	91500-1	91500-3
		20-18	0.5-0.8	91508-1	91508-3
		16-14	1.25-2	91506-1	91506-3
	Mini-Universal	20-16	0.5-1.25	91536-1	91536-3
	Mini-Universal II Contacts	26-22	0.12-0.3	91529-1	91529-1
		22-18	0.3-0.8	91522-1	91523-3
20-16		0.5-1.25	91594-1	91594-3	
MR Connectors	Contacts	26-18	0.12-0.8	91526-1	91526-3

*Head may be disassembled from tool assembly.

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.

124208 06/18 Original

Contact us today to learn more

E-mail (Americas): fieldservicesnorthamerica@te.com

Phone (Americas): 800-722-1111 or 717-986-3434

E-mail (EMEA): TEFE1@te.com

Phone (EMEA): +49-6151-607-1518

For additional information download catalog no.

1-1307619-0 from tooling.te.com.

www.te.com