



LOW PRESSURE

Intrinsically Safe Transducer AST44I P

Overview

The AST44LP is a stainless steel pressure transducer with a wide variety of options. With its rugged construction and the best price-to-performance ratio in the industry, the AST44LP is the solution for low pressure measurement in Intrinsically Safe areas.

Benefits

- Class I Div 1 Intrinsically Safe Groups C, D when installed with an approved barrier
- ATEX / IECEx: Class I Zone 0 Exia IIB T4 Ga (Ta = -40°C to +80°C)
- High Strength Stainless Steel Construction
- No Internal O-rings
- Wide Operating Temperature
- Pressures from 0-1 to 0-15 PSI
- Low Static and Thermal Errors
- Unparalleled Price and Performance
- Compatible with Wide Variety of Liquids and Gases

Applications

- Industrial OEM Equipment
- HVAC/R Equipment
- Water Management and External Tank Levels
- Control Panels
- Pneumatics and Hydraulic Systems
- Vapor Recovery
- Data Loggers

Environmental Data

Ambient Temperature: 25°C (77°F) (Unless otherwise specified)

Operating Ambient	-40 to 80°C (-40 to 176°F)
Storage	-40 to 100°C (-40 to 212°F)

Electromagnetic Compatibility (EMC)

Standard	Description	Test Value
EN55011	Radiated Emissions	Class A, 30-1000 MHz
EN61000-4-2	Electrostatic Discharge Immunity	±8 kV Air Discharge
		±4 kV Contact Discharge, VCP, HCP
EN61000-4-3	Radiated Electromagnetic Field Immunity	10V/m, 30-2700 MHz 80% 1kHz AM Modulation
EN61000-4-4	Electrical Fast Transient/Burst	±0.5 kV, ±1 kV, ±2 kV on DC Mains
	Immunity	±0.5 kV, ±1 kV on I/O Ports
EN61000-4-5	Surge Immunity	±0.5 kV,±1 kV, on I/O Ports & DC Lines
EN61000-4-6	Conducted immunity	10V rms, 0.15-80 MHz, DC Mains
		10V rms, 0.15-80 MHz, I/O Ports
		80% 1kHz AM Modulation
EN61000-4-8	Power Frequency Magnetic Field Immunity Test	30 A/m @ (50Hz, 60Hz) 3 orthogonal orientations

Shock, Vibration & Ingress Protection (IP)

Standard	Description	Test Value
EN 60067-2-27	Shock Test	500m/s², 6ms, half sine-wave, 6 shocks (3/direction), horizontal and vertical axis, 12 total shocks
EN 60068-2-6	Sinusoidal Vibration	5-25 Hz, 2mm, 25-150 Hz, 50m/s, Sweep rate: 1 octave/min, Duration: 24 hours/axis (48 hours total), horizontal and vertical axis
EN 60068-2-64	Random Vibration	10-2000 Hz, vibration level: 0.0314 (m/s²)²/Hz, 24 hrs/axis (48 hrs total), 2 directions: horizontal and vertical
IEC 60068-2-32	Drop Test	Drop of 1 meter to floor made of concrete. Dropped twice on the threaded end and two times perpendicular to the threaded end.
IP-66	Ingress Protection	Dust-tight, protected against powerful water jets

Performance

Ambient Temperature: 25°C (77°F) (Unless otherwise specified)

Parameters	MIN	ТҮР	MAX	UNITS	NOTES
Accuracy	-0.25		+0.25	%Span	1
Accuracy (1 PSI)	-0.50		+0.50	%Span	1
Zero Error	-1.0		+1.0	%Span	2
Span Error	-1.5		+1.5	%Span	3
Span Error (4-20mA)	-2.0		+2.0	%Span	3
Thermal Error, Zero	-1.5		+1.5	%Span	4
Thermal Error, Span	-1.5		+1.5	%Span	5
Stability (1 year)		±0.25		%Span	
Proof Pressure		2X Rated Pressure		PSI	6
Burst Pressure		5X Rated Pressure or 75 (whichever is less)		PSI	7
Compensated Temp. Range		0 - 55° (32 to 132°)		°C (°F)	

Electrical Data


Model	AST44LP				
Output	4-20mA	1-5V, 1-6V			
Excitation	10-28VDC	10-28VDC			
Output Impedance	> 10k Ω	< 100 Ω			
Current Consumption	-	<10mA			
Output Noise	-	<2mV RMS			
Output Load	0-800Ω	10k Ω Min.			
Reverse Polarity Protection	Yes	Yes			
Bandwidth	DC-250 Hz	DC-1kHz			


Notes


- 1. The maximum deviation from a best fit straight line (BFSL) fitted to the output measured over the pressure range at 25°C. Includes all errors due to pressure non-linearity, hysteresis, and non-repeatability. Span is the algebraic difference between full scale output and zero pressure offset.
- 2. The maximum variation from the ideal offset measured at 25°C.
- 3. The maximum variation from the ideal full-scale span measured at 25°C.
- 4. The maximum variation of offset within the compensated temperature range relative to 25°C.
- 5. The maximum variation of full-scale span within the compensated temperature range relative to 25° C.
- 6. The maximum pressure that can be safely applied to the product tor it to remain in specification once pressure is returned to the operating pressure range.
- 7. The maximum pressure that can be applied without causing escape of the pressure media.


Dimensions & Electrical Connection

Unless otherwise specified, all dimensions are in inches










UL Approved Barrier Installation / A01657



The transducers listed below are designed for installation in EITHER Class I, Division 1, Groups C,D; Class I, Zone 0 Group IIB DR Class I, Division 1, Groups A,B,C,D; Class I, Zone 0 Group IIC hazardous locations when connected to Associated Apparatus as described in note 1.

Entity Parameters

Models AST4400, AST44LP, AST4500, AST4510, AST4520 Class I, Div. 1, Groups C,D; Class I, Zone 0 Ex ia IIB T4; Class I, Zone 0 AEx ia IIB T4 \sqrt{N}

Model AST4401 Class I, Div. 1, Groups A,B,C,D; Class I, Zone 0 Ex ia IIC T4; Class I, Zone 0 AEx ia IIC T4 Vnax = 14.5V


4-20mA with upto 1000ft of connector integral cable integral cable connector integral cable integral

Isc or Io is the total current available from the Associated Apparatus under any condition.

1. The following conditions must be satisfied:

- 2. Control Room aparatus shall not generate in excess of 250V (Umax).
- Canadian installations should be in accordance with Canadian Electrical Code, Part I. U.S. installations should be in accordance with Article 504 in the National Electrical Code, ANSI/NFPA 70.

CSA Approved Barrier Installation / A08949



Entity Parameters

Models AST4400, AST44LP, AST4500, AST4510, AST4520, AST4530 Class I, Div. I, Groups C,D; EXia IIB, T4; Class I, Zone 0, AEXia IIB, T4 \sqrt{N} = 28 \sqrt{M} c

Model AST4401 Class I, Div. 1, Groups A,B,C,D; EXIa IIC, T4; Class I, Zone 0, AEXIa IIC, T4 Vnax = 14.57vic

4-20mA with	4-20mA with upto 1000ft of integral cable	All EXCEPT 4-20mA	All EXCEPT 4-20mA
integral		with integral	with upto 150ft of
connector		connector	integral cable
Pmax = 625 mW	Pmax = 625 mW	Pmax = 625 mW	Pmax = 625 mW
Imax = 93 mA	Imax = 93 mA	Imax = 93 mA	Imax = 93 mA
CI = 0.391 uF	CI = 0.434 uF	CI = 0.643 uF	Cl = 0.649 uF
Li = 0	Li = 155 uH	Li = 0	Li = 23.3 uH

- For installation in accordance with Fig 2, barrier nust be a CSA Certified, Single Channel grounded Shunt-Blode Zener Barrier or a Single Channel Isolating Barrier.
- For installations in accordance with Figs. 1 and 3, one dual-channel or two single-channel barriers may be used, where in either case, both channels have been Certified for use together with combined entity parameters.
- 3. The following conditions must be satisfied:

- 4. Maximum non-hazardous area voltage must not exceed 250 ${\sf V}.$
- Canadian installations should be in accordance with Canadian Electrical Code, Part I. U.S. installations should be in accordance with Article 504 in the National Electrical Code, ANSI/MPR 20.
- 6. A grounding method is not provided by the manufacturer as part of the integral design of the Transducer. For units which are connected through a grounded shunt diode safety barrier, ensure that the transducer is mounted to a surface which is at the same potential as the barrier ground.
- 7. See user manual for installation conditions

Note: Float unused wires in cable. Insure that these wires are electrically isolated from other conductors



Available Process Connection, Material Configurations & Pressure Codes

316L PSI

Droccuro Pango	Drossuva Danga Cada	PSI Unit	Process Connection Code					
Pressure Range	Pressure Range Code		Α	С	1	P		
0 - 1	00001	Р	√	✓	✓	✓		
0 - 2.5**	00069	Н	✓	✓	✓	✓		
0 - 5	00005	Р	✓	✓	✓	✓		
0 - 7.5**	00208	Н	✓	✓	✓	✓		
0 - 10	00010	Р	√	✓	✓	√		
0 - 15	00015	Р	✓	✓	✓	✓		

Hastelloy PSI

Proceuro Pango	Duassura Danga Cada	DCI IImit	Process Connection Code					
Pressure Range	Pressure Range Code	PSI Unit	Α	С	1	Р		
0 - 1	00001	Р	X	X	X	X		
0 - 2.5**	00069	Н	Х	Х	Χ	✓		
0 - 5	00005	Р	Х	Х	Χ	✓		
0 - 7.5**	00208	Н	X	Х	Χ	✓		
0 - 10	00010	Р	X	Х	X	√		
0 - 15	00015	Р	X	Х	X	✓		

^{*}See Ordering Information for list of options. **Must in ordered in inches H_2O

Ordering Information

AST44LP		Α	00005	Р	4	E	1	000	-ss
Process Connection A= 1/4" NPT Male C= 1/4" BSPP Male I= 1/4" NPT Female P= 1/2" NPT Male									
Pressure Range Insert Pressure Range Code (see tab	le for availability)								
Pressure Unit P= PSI H= Inches H ₂ O									
Output 3= 1-5V 4= 4-20mA (2 wire loop powered) 6= 1-6V									
Electrical Connection A= 2 ft. (0.6m) B= 4 ft. (1.2m) C= 6 ft. (1.8m) D= 10 ft. (3.0m) E= Mini DIN 43650C F= Packard Metripack 150 3-Pin I= DIN 43650A	L= Conduit, Cable 2 ft. (0.6 m) M= Conduit, Cable 4 ft. (1.2 m) N= Conduit, Cable 6 ft. (1.8 m) P= Conduit, Cable 10 ft. (3 m) R= 6- Pin Bendix Y= M12x1 4 = Mini-Fast (-SS Only)								
Wetted Material 1= 316L									
Options Codes 000= No Options									
Approval Type									
Leave UL ANSI/ISA 12.12.01 Class I Blank (formerly UL913)]	Div 1 Intrinsically Safe Groups C, D								
Not available for Electrical Con	nection 4								

Note: CSA approved products require case/earth ground electrical connection. See wiring installation sheet for further details

NORTH AMERICA

American Sensor Technologies, Inc. (AST), a TE Connectivity Company Tel: 800-522-6752

Email: <u>customercare.molive@te.com</u>

ASIA

Hong Kong Sensor Technologies (HKST), a TE Connectivity Company Tel: 0400-820-6015 Email: customercare.shzn@te.com

TE.com/sensors

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.