


REVISIONS			
REV	DESCRIPTION	DATE	APPV
A	PRODUCTION RELEASE	JHAGER 5/5/21	DV 5/7/21



- NOTES: (UNLESS OTHERWISE SPECIFIED)
- ALL DIMENSIONS ARE IN MILLIMETERS [IN].
 - DIMENSIONS APPLY AFTER FINISHING.
 - MANUFACTURE TO BE COMPLIANT WITH EU RoHS DIRECTIVE, USE MATERIALS THAT DO NOT CONTAIN REACH SUBSTANCES OF VERY HIGH CONCERN >1000ppm, AND USE DRC CONFLICT-FREE SOURCED MATERIALS.
 - ELECTRICAL PROPERTIES SHOWN FOR REFERENCE ONLY. SEE LINX DATA SHEET FOR ELECTRICAL PERFORMANCE DATA.
 - RADIATION PATTERN: OMNI-DIRECTIONAL
 - IMPEDANCE: 50Ω
 - VSWR: <3.5 ALL BANDS.
 - MAX POWER: 10W
 - PRODUCT QUALIFIED IAW LINX INTERNAL TEST PLAN AT LATEST REVISION.
 - MECHANICAL
 - INTERFACE IAW SMA TYPE. MIL-STD-348B
 - ALL UNLISTED GEOMETRY CONTROLLED BY SOLID MODEL AT LATEST REVISION.
 - TEMPERATURE RANGE: -20°C-+65°C
 - PACKAGE ANTENNAS INDIVIDUALLY AND SHIP IN LOT BAGS OF 50 PC.
 - LABELING TO INCLUDE THE FOLLOWING INFORMATION ONLY ON ALL LOT BAGS, AND BOXES.
 - LOT NUMBER
 - LINX PART NUMBER
 - QUANTITY
 - COUNTRY OF ORIGIN

WARNING: THIS DRAWING CONTAINS PROPRIETARY INFORMATION THAT IS THE SOLE PROPERTY OF LINX TECHNOLOGIES, AND SHALL BE TREATED AS SUCH. NO DISCLOSURE OR REPRODUCTION OF THIS DOCUMENT IS PERMITTED, IN WHOLE OR IN PART, WITHOUT THE EXPRESS WRITTEN PERMISSION OF LINX TECHNOLOGIES OR ITS DESIGNATED AGENTS.

STE connectivity 159 ORT LANE
MERLIN, OR 97532

TITLE: LTE, LTE-M, NBIOT Dipole Tilt Swivel Antenna, SMA Connector

MATERIAL: ABS	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5. .X ±2.0 .XX ±1.00 .XXX ±.500	ANGLES: ±1° SURFACE: √	PROJECTION:
WEIGHT:	DRAWN: JHAGER	DT: 5/5/21	SIZE DWG. NO. REV B C-ANT-W63WS3-SMA A
FINISH: BLACK TEXTURE	ENGR: DASARATHAN	DT:	SCALE: 1:1 DO NOT SCALE DRAWING SHEET 1 OF 1

LDCDFB_B