





P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER PCN-E-16-016968	13DEC2016	MGM	DM



RECOMMENDED CUTOUT

- 7. FLANGE SEAL IS CUSTOMER SUPPLIED.
 - 6. SURFACE FINISH: 32 RMS OR BETTER; .005 [.12]
 - 5. THIS RECEPTACLE MATES WITH DRC16-40S-XXXX. (XXXX = ALL MODIFICATIONS)
 - 4. CONTACT PLATING - MATING AND SOLDER CUP SIDES: TIN
 - 3. MATERIAL - HOUSING: PLASTIC; SEAL: RUBBER; INSERT: STEEL
 - 2. RECEPTACLE IS SUPPLIED WITH DUST CAP (NOT SHOWN).
 - 1. DIMENSION TOLERANCE: ±.025 [.64]; CUTOUT: ±.010 [.25]
- NOTES: UNLESS OTHERWISE SPECIFIED



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	V. TOMSA	08SEP2003	 TE Connectivity	NAME RECEPTACLE, FLANGED SOLDER POT 40 #16 SIZE CONTACTS DRC SERIES COLOR: BLACK					
DIMENSIONS: in [mm]		CHK	X. SANCHEZ	24SEP2003							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D. MEYER	24SEP2003							
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH ±-		PRODUCT SPEC	-	-							
MATERIAL	3	WEIGHT	112 (g)	SIZE	A3	CAGE CODE	4AFU8	DRAWING NO	©-DRC10-40P	RESTRICTED TO	-
CUSTOMER DRAWING			SCALE	1:1	SHEET	1	OF	1	REV	G	