


3D VIEW

SCALE 1:1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-008761	10JUN2014	DM	DM
	A1	REVISED PER PCN E-18-018863	30NOV2018	JA	DM
	A2	REVISED PER PCN E-19-009181	11JUN2019	JA	IG



4 SMALL MATERIAL EXTENSION IS ACCEPTABLE ON THIS END ALL AROUND.

3. THIS ACCESSORY PART IS PROVIDED WITHOUT TYPICAL TRANSPORTATION INDUSTRY PROCESS CONTROLS. NO VALIDATION TESTING HAS BEEN PERFORMED. CUSTOMER IS RESPONSIBLE FOR DETERMINING PRODUCT PERFORMANCE AND SUITABILITY FOR APPLICATION.

2. TEMPERATURE RATING: -29°C TO +100°C [-20°F TO +212°F].

1. THIS PART IS USED ON DT04-4P WITH ANY MODIFICATION.

NOTES:

TE INTERNAL PN	DEUTSCH PN
DT4P-DC	DT4P-DC

2018 RELEASED FOR PUBLICATION ALL RIGHTS RESERVED. THIS DRAWING IS UNPUBLISHED. BY TE CONNECTIVITY © COPYRIGHT 2014

DIMENSIONS: mm [INCHES]	DWN D.MEYER	10JUN2014	MATERIAL PVC	FINISH GRAY
	CHK R.MESSENGER	10JUN2014	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D.MEYER	10JUN2014		
	0 PLC ±	PRODUCT SPEC	SIZE A 4	CAGE CODE 4AFU8
1 PLC ±	APPLICATION SPEC	RESTRICTED TO	-	
2 PLC ±	WEIGHT 2.98 g	CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
3 PLC ±0.63 [.025]			REV A2	
4 PLC ±				
ANGLES ±0° 30' 0"				