

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# KAPTON LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
T1K	C73746-000	T1K-178095-10-9	KP228, Kapton white gloss (0,063 mm), Acrylic adhesive	TTDS-034

Quantity per roll: 10.000 PCs

Labels across: 4

Winding: outside






length of roll: 31,8 m



KAPTON SERIES

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity													
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,12]	DIMENSIONS mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED	CHK S. Iser / 01.04.2020 DATE														
	ADHESIVE	LABEL WIDTH:	±0,3 [0,12]				APVD S. Iser / 01.04.2020 DATE														
	LINER	WEB WIDTH:	±0,8 [0,31]	<table border="1"> <tr> <td>0 PLC</td> <td>± -</td> </tr> <tr> <td>1 PLC</td> <td>± -</td> </tr> <tr> <td>2 PLC</td> <td>± -</td> </tr> <tr> <td>3 PLC</td> <td>± -</td> </tr> <tr> <td>4 PLC</td> <td>± -</td> </tr> <tr> <td>ANGLES</td> <td>± -</td> </tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	Name		Kapton Label Size „178095“	
0 PLC	± -																				
1 PLC	± -																				
2 PLC	± -																				
3 PLC	± -																				
4 PLC	± -																				
ANGLES	± -																				
		VERTICAL REPEAT:	±0,8 [0,31]*	MATERIAL		FINISH		GLOSS UNPRINTED MATT PRINTED													
		HORIZONTAL REPEAT:	±0,8 [0,31]*	SEE TABLE				CUSTOMER DRAWING													
		PRINT POSITIONING:	±0,8 [0,31]*					SHEET 1 of 1													
		LEFT MARGIN:	±0,4 [0,16]					REV A1													
		QUANTITY:	-0% +2%																		
		*NON ACCUMULATING																			