





REVISIONS				
P	LTN	DESCRIPTION	DATE	APPD
A		INITIAL	03JUN2016	RL CW
A1		ECR-16-012141	30AUG2016	RL CW
A2		ECR-16-015006	26OCT2016	RL CW
B		ECR-20-014403	20MAY2021	BS CW



NOTES:
 1. TECHNICAL CHARACTERISTICS:
 HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
 SURFACE TREATMENT: POWDER COATED, BLACK
 DEGREE OF PROTECTION: IP68 (MATED)

注释:
 1. 技术参数:
 壳体材料: 铝合金
 表面处理: 黑色粉末喷涂
 防护等级: IP68 (配合)



T1926240150-000	H24BPR-TGXH-4S-M50	H24BPR HEIGHTEN HOOD, QUADRANGLED LOCKING, TOP ENTRY M50, POWDER COATED, BLACK H24BPR加高上壳, 四角锁定, 顶出M50, 黑色粉末喷涂	M50
T1926240163-000	H24BPR-TGXH-4S-M63	H24BPR HEIGHTEN HOOD, QUADRANGLED LOCKING, TOP ENTRY M63, POWDER COATED, BLACK H24BPR加高上壳, 四角锁定, 顶出M63, 黑色粉末喷涂	M63
PART NUMBER 料号	PART DESCRIPTION 描述		PG/M THREAD PG/M螺纹孔

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN ROY LIU	03JUN2016	STE TE Connectivity
CHK KYLE ZENG	03JUN2016	
APVD CHRIS WANG	03JUN2016	NAME H24BPR-TGXH-4S-MXX
DIMENSIONS: mm		PRODUCT SPEC 108-137014
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-137014
0 PLC	±	SIZE A1
1 PLC	±	CAGE CODE
2 PLC	±	DRAWING NO C-T19262401XX00X
3 PLC	±	RESTRICTED TO
4 PLC	±	SCALE 1:1
ANGLES	±	SHEET 1 OF 1
MATERIAL		REV B
FINISH		CUSTOMER DRAWING