

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	02NOV2017	RL	CW
	B	ECR-17-017888	14DEC2017	RL	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:  
 INSULATION MATERIAL: PC  
 RATED VOLTAGE: 500V  
 RATED CURRENT: 16A  
 INSULATION RESISTANCE:  $\geq 400M\Omega$   
 RATED IMPULSE VOLTAGE: 6KV  
 POLLUTION DEGREE: 3  
 FLAMMABILITY: UL94V-0  
 MATING CYCLES: 500 CYCLES  
 WIRE RANGE:  $0.5mm^2 \sim 2.5mm^2$  (AWG20-AWG14)  
 CONTACT TYPE: SPRING CLAMP

M4 screw, recommended  
tightening torque 1.2Nm  
M4 螺丝, 推荐锁紧力矩为1.2Nm

注释:

1. 技术参数:  
 绝缘材料: PC  
 额定电压: 500V  
 额定电流: 16A  
 绝缘电阻:  $\geq 400M\Omega$   
 脉冲电压: 6KV  
 污染等级: 3  
 阻燃等级: UL94V-0  
 插拔次数: 500 次  
 接线范围:  $0.5mm^2 \sim 2.5mm^2$  (AWG20-AWG14)  
 接线类型: 弹片压接

4 X M3 screw, recommended  
tightening torque 0.5Nm  
4 X M3 螺丝, 推荐锁紧力矩为0.5Nm

Panel cut out for inserts for  
use without hoods/housings  
不使用防护外壳时芯件的安装开孔图

T2040063101-001	HE-006-MS	HE-006 MALE INSERT, SPRING CLAMP, NO LOGO HE-006公插, 弹片, 无LOGO
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROY LIU 02NOV2017		NAME HE-006-MS
		CHK GINO YAO 02NOV2017		
		APVD CHRIS WANG 02NOV2017		
		PRODUCT SPEC 108-137044		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-137044
		0 PLC ±-		WEIGHT -
		1 PLC ±-		SIZE A3
		2 PLC ±-		CAGE CODE 00779
		3 PLC ±-		DRAWING NO T2040063101001
		4 PLC ±-		RESTRICTED TO -
		ANGLES ±-		SCALE 1:1
MATERIAL -		FINISH -	SHEET 1 OF 1	
			REV B	
			CUSTOMER DRAWING	

1470-19 (3/13)