

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

LOC

DIST

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

J

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

A1

REVISED

ECR-14-011195

24JUL2014

TS

KB

-1; AS SHOWN

SECT. A-A

SECT. B-B

注：
1. 適用圧着規格番号：114-5193

NOTE：
1. APPLICABLE CRIMPING SPEC No. 114-5193

TOLERANCE UNLESS OTHERWISE SPECIFIED:
一般公差
0 < x ≤ 10 : ±0.2
10 < x ≤ 30 : ±0.25
30 < x ≤ 100 : ±0.3
ANGLE : ±3°
角度

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -

MATERIAL: BRASS
FINISH: PRE-TIN

DWN	T.SHINOHARA	7/31'95
CHK	K.YUASA	7/31'95
APVD	A.TOMITA	7/31'95
PRODUCT SPEC	-	-
APPLICATION SPEC	-	-
WEIGHT	0.06 g	-
CUSTOMER DRAWING		

WIRE RANGE 抱合電線断面積	AWG #22~#20 (0.3~0.5)	INSULATION DIA 被覆外径	1.4~1.7
TE Connectivity			
NAME TAB CONTACT (MINI MULTI LOCK CONNECTOR)			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-917309	-
SCALE 10:1		SHEET 1 OF 1	REV A1

1470-19 (3/11)