

For More Information

TE Technical Support Center

North America	+1 800 522 6752
Asia Pacific	+86 0 400 820 6015
Austria	+43 1 905 601 228
Baltic Regions	+46 8 5072 5000
Benelux	+31 73 6246 999
Czech Republic	+420 800 701 462
France	+33 1 34 20 86 86
Germany	+49 6251 133 1999
Hungary	+36 809 874 04
Italy	+39 011 401 2632
Nordic	+46 8 5072 5000
Poland	+48 800 702 309
Russia	+7495 790 790 2
Spain/Portugal	+34 93 2910366
Switzerland	+41 52 633 66 26
United Kingdom	+44 800 267 666

Follow us on Twitter for all the latest product news
@TEConnectivity, and on Facebook, TEConnectivity.

te.com/highspeed

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved.

1-1773862-2 ADM/RRD 1M 08/2015

AMPLIMITE, CeeLok FAS-T, CeeLock FAS-X, DEUTSCH, Mircodot, NANONICS, TE, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications.



QUICK REFERENCE GUIDE

High Speed

- Achieve signal integrity
- Support a wide range of high-speed protocols for networking, video, and storage

Rugged

- Meet the demands of harsh environments

Compact

- Save weight and space



Protocol	CeeLok FAS-T Connectors	CeeLok FAS-X Connectors 11-08	CeeLok FAS-X Connectors 25-32	CeeLok FAS-T Nano Connectors	Quadrx Connectors	DEUTSCH D38999 Connectors	DEUTSCH Wildcat 38999 Connectors	Deutsch Wildcat Micro 06-09 Connectors	MTC Connectors	Deutsch ABC Connectors	Deutsch DMC-M Connectors	Microdot Micro-D Connectors	NANONICS Nanominiature Rectangular Connectors	AMPLIMITE M24308 D-Sub Connectors
Ethernet (10BASE-T)	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable
Fast Ethernet (100BASE-T)	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable
Gigabit Ethernet (1000BASE-T)	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable
10 Gigabit Ethernet (10GBASE-T)	Suitable	Suitable	Suitable	Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Suitable	Not Suitable
IEEE 1394b	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable
USB 2.0	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable
USB 3.0	Not Suitable	Not Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Not Suitable
SATA 1.0	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Suitable	Not Suitable	Suitable	Suitable	Suitable	Suitable	Suitable
SATA 2.0	Not Suitable	Not Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Not Suitable
SATA 3.0	Not Suitable	Not Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Not Suitable
HDMI	Not Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Suitable	Suitable
DVI-D	Not Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Not Suitable	Suitable	Suitable*	Suitable	Suitable	Suitable	Suitable
Display Port 1.0	Not Suitable	Not Suitable	Suitable	Not Suitable	Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Not Suitable
Display Port 1.2	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Not Suitable	Suitable	Suitable	Not Suitable

*DVI-D Single Only



The information contained herein and the data used in this analysis are applicable solely to the specified TE Connectivity (TE) products as dated by the document using current standard industry practices and application techniques. All information should be verified that it is representative of the current implementation of the customer's application of the connector. Alternative connectors may be compatible, but their electrical performance may vary significantly, due to construction, material characteristics, or termination techniques. Usage of the information for any other connector or previous implementation is improper, and TE disclaims any and all liability or potential liability with respect to such usage.