



DRAWING MADE IN AMERICAN PROJECTION

⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

NUMBER C-160718




.020 MAX
(0.5)




.020 MAX
(0.5)

FOR .020 TAB-THICKNESS
(0.5)



.010
(0.25)



⚠ FOR AMP-D-TATOR APPLICATION

⚠ REELED WITH PAPER COVER

160718-9	⚠	BRASS	PRETIN	⚠
160718-8	⚠	BRASS	—	⚠

CUSTOMER COPY FOR REFERENCE ONLY

160718-5	⚠	PHOSPHOR BR	—	—
160718-4	⚠	BRASS	PRETIN	⚠
160718-3	⚠	BRASS	SILVER	—
160718-2	⚠	BRASS	PRETIN	—
160718-1	⚠	BRASS	—	—

©1977 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED
AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



AMP-HOLLAND N.V.
HERTOGENBOSCH
HOLLAND

WIRE RANGE 0.5-10 mm	INSUL RANGE 0.00-140/2X0.80 20-36 / 2x20	FIRST USED
SCALE 4 ≈ 1	LOC H	SIZE A
NO C-160718		REV E2

ORDER NO.	MATERIAL	PLATING
DR R 13/11-77	DATE	DATE
CHK	DATE	DATE

NAME 110 Ser FASTON RECEPTACLE

DIMENSIONS IN (MM) INCHES (DO NOT SCALE PRINT)