## SPECIFICATION CONTROL DRAWING

5022W1041



.095

.112

.128

.318

± .007

50 OHM, AWG 22, 19 STRANDS OF AWG 34, WATERBLOCKED, COAXIAL CABLE

Date: Revision: С

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200

CONSTRUCTION DETAILS

**ELECTRICAL CHARACTERISTICS** 

DIMENSIONS ARE NOMINAL VALUES IN INCHES, UNLESS OTHERWISE DESIGNATED.

CHARACTERISTIC IMPEDANCE 50 ± 2 ohms, Method A CAPACITANCE 29.4 pF/ft. (nominal)

VELOCITY OF PROPAGATION 69% (nominal)

**VOLTAGE RATING** 1400 volts (rms) (maximum)

CONDUCTOR .0315 AWG 22, 19 Strands of AWG 34, Tin-Coated Copper **DIELECTRIC** 

> Modified FEP Color - White

**SHIELD** 

AWG 38.

Tin-Coated Copper

WATERBLOCK LAYER

Non-Woven PET

Water Sealant filling

shield interstices

**JACKET** 

Thermorad NTFR

## ADDITIONAL REQUIREMENTS

**ELECTRICAL** 

CONDUCTOR RESISTANCE 15.5 ohms/1000 ft. (nominal)

**INSULATION RESISTANCE** 

(DIELECTRIC) 10,000 megohms (minimum) for 1000 ft.

JACKET RESISTANCE 20 megohms (minimum) for 20 meters

JACKET FLAWS

SPARK TEST 1.0 kV (rms) IMPULSE TEST 6.0 kV (peak)

**VOLTAGE WITHSTAND** 5000 volts (rms) (minimum)

(DIELECTRIC)

**PHYSICAL** 

INSULATION (DIELECTRIC)

**ELONGATION** 150% (minimum) TENSILE STRENGTH 1000 lbf/in<sup>2</sup> (minimum)

**JACKET** 

**ELONGATION** 200% (minimum)

TENSILE STRENGTH 1300 lbf/in2 (minimum) JACKET THICKNESS .095 inch (nominal)

SHIELD COVERAGE 90% (minimum) WATERBLOCKING 1 inch3 (maximum)

(per Raychem Spec 345)

**WRAP** .004 inch thick (nominal)

CABLE IDENTIFICATION:

Outer jacket shall be marked in contrasting color at 12 inch (nominal) intervals

between marks as follows: "5022W1041 RAYCHEM 06090"

WEIGHT 52.5 lbs/1000 ft. (nominal)

Designate outer jacket color with a dash number in accordance with MIL-STD-681. Unless otherwise specified, outer jacket color will be black designated by a "-0" appended to the part number, e.g. 5022W1041-0.

Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.

**ENGINEERING REFERENCE** 

TEMPERATURE RATING 90°C

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

Page 1 of 1

Thermorad, Cheminax, Raychem, TE Connectivity, and TE connectivity (logo) are trademarks.

