
SPECIFICATION CONTROL DRAWING

SCD 55A6470

TWO CONDUCTOR CABLE, DOUBLE SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT

Date 3-6-18 Revision

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



CABLE CONSTRUCTION DETAILS								
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)		JACKET THICKNESS (inch)		OUTSIDE DIAMETER (inch)		MAXIMUM WEIGHT (lbs/1000 ft.)
	,	INNER	OUTER	MINIMUM	NOMINAL	NOMINAL	MAXIMUM	,
55A6470-22-*	22	38	38	.006	.008	.144	.151	19.8
55A6470-20-*	20	38	38	.006	.008	.158	.166	24.6

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature VOLTAGE RATING: 600 volts (rms) at sea level ACCELERATED AGING: 300 ± 3°C for 7 hours

BLOCKING: 200 ± 3°C for 6 hours **DIELECTRIC WITHSTAND:**

1500 volts (rms), 60 Hz, conductor to conductor and shield FLAMMABILITY: Procedure 1,

3 seconds (maximum), 3 inches (maximum); no flaming of facial tissue

JACKET COLOR: White preferred

JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

JACKET FLAWŠ:

Spark Test, 1000 volts (rms)

Impulse Dielectric Test, 6.0 kV (peak)

LIFE CYCLE: 200 ± 3°C for 168 hours

LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours

SHIELD COVERAGE: 85% (minimum) (each) VOLTAGE WITHSTAND (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

WRAP: .002 inch thick (nominal), 25% overlap (minimum)

1/ PART NUMBER:

The "*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 22. blue and white component wires:

white jacket: 55A6470-22-6/9-9

NOTE: Nominal values are for information only. Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "AXXX".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Raychem, TE Connectivity, and TE connectivity (logo) are trademarks.

Page 1 of 1

DIMENSIONS ARE IN INCHES AND, UNLESS OTHERWISE DESIGNATED, ARE NOMINAL

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN. REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID



Raychem Wire & Cable 501 Oakside Avenue Redwood City, CA 94063-3800 Phone: 1-800-522-6752 Fax: 1-650-361-6297