D

С

В

А

4

2

| _ | | | | | | | |
|---|-------------------------|--|-----------|-------|------|--|--|
| | | REVISIONS | | | | | |
| | P LTR | DESCRIPTION | DATE | DWN | APVD | | |
| | A | INITIAL RELEASE | 02APR2021 | BS | СВ | | |
| | | | | | | | |
| | _ | | | | | | |
| | | | | | | | |
| R W AG | ENCY. | <u>NS</u> E FORMALLY RECOGNIZED, CERTIFIED OR THEREFORE, ALL TEST/REQURIEMENTS SP THE FOLLOWING AGENCY STANDARDS WILL | ECIFIED | ΙΝΤ | ΉE | | |
|) [D | | 8A 440V 50Hz/60Hz 40°C 8A 440V 50Hz/60Hz 40°C | | | | | |
| IT / | CIFIC VOLTA Y: 50 | GE: 8A, 440VAC | | | | | |
| κA | GE CU | RRENT: 18mA @ 230VAC, 50Hz | | | | | |
| MB | IENT | TEMPERATURE RANGE @ RATED CURRENT: - | 25°C TO | +40°(| C | | |
| INT, Ta, HIGHER THAN 40°C, THE MAXIMUM OPERATING IS AS FOLLOWS: $Io=Ir-\sqrt{\frac{85-Ta}{45}}$ | | | | | | | |
| 1 P E | RATUR | V 45 E: -40°C TO +85°C @ 40°C AND 95% RH | | | | | |
| | ATION OMINA | <u>S</u> L: 9mH | | | | | |
|) U N | | MINAL: 1.1μF NAL: 1μF | | | | | |
| RES 1Ω 1Ω (χ (χ | ISTOR 1W 1W | | | | | | |
| | RGE R | ESISTOR) 20°C, 50% RH AND 100VDC, MI | N: 6ΜΩ | | | | |
|)UN | D FOR | <u>ING INSPECITON HIPOT</u> 1 MINUTE: 2632VDC MINUTE: 1892VDC | | | | | |
| | <u>'Al</u> to se | LECT AND QUALIFY A FILTER IS FOR YOU | R | | | | |

SAFETY ORGAI THIS FILTER THE LISTED LATEST REVI

UL APPROVED

CSA APPROVEI

OPERATING SI LINE CURRENT LINE FREQUEN

MAXIMUM LEAH

OPERATING AN

IN AN AMBIEI CURRENT, Io,

RELIABILITY STORAGE TEMI HUMIDITY: 2

TEST SPECIF INDUCTANCE,


CAPACITANCE LINE TO GROU LINE TO LIN

DISCHARGE RI L/G I.R. 1M(L/L I.R. 2MG L/N I.R. XX> N/G I.R. XX> IR (NO DISC

RECOMMENDED LINE TO GROU


FILTER APPRO THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.

| THIS DRAWING IS A C | ONTROLLED DOCUMENT. | DWN 02APR2021 BAPAT SAHAS CHK DIC DOUZAPR2021 | |
|---------------------|---|---|-----------------------|
| dimensions: MM | TOLERANCES UNLESS OTHERWISE SPECIFIED: | CHRIS BOLLE APVD 02APR2021 CHRIS BOLLF | NAME POW |
| | 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.40 3 PLC ±0.130 4 PLC ±0.0500 ANGLES ±- | PRODUCT SPEC - APPLICATION SPEC - | DIN 8KE size ca |
| MATERIAL - | FINISH - | WEIGHT _ | A 300 |
| - | - | CUSTOMER DRAWING | |
| | | | |



TYPICAL INSERTION LOSS COMMON MODE 50/50 Ω ; DIFFERENTIAL MODE 50/50 Ω

| MHz | 0.01 | 0.05 | 0.15 | 0.5 | 1 | 3 | 5 | 10 | 30 |
|-----|------|------|------|-----|----|----|----|----|----|
| СМ | 56 | 60 | 62 | 54 | 50 | 42 | 40 | 34 | 32 |
| DM | 20 | 24 | 35 | 60 | 46 | 39 | 36 | 30 | 26 |



470-19 (3/13)

E TE TE Connectivity ER LINE FILTER FOR 35 RAIL INSTALLATION А MS10AFPDVM GE CODE DRAWING NO RESTRICTED TO 779 C - 7 - 1609967 - 4 REVA 2:5 SHEET SCALE 1 ^{OF} 2

| | 4 | 3 | | | 2 | | | | | | | | | |
|---|--|------------------|---|-----------------------|--|--|----------------|----------------------------|--|-------------------------------|------|---------------------------|------|---|
| | C 2021 TE Connectivity. All Rights Reserved. | 1 | | | | | | | REVISIONS | | | | | |
| D | NOTE 1 GROUND CONNECTION: FOR ELECTRICAL SAFETY AND FILTER PERFO UNIT MUST HAVE A GOOD GROUND CONNECTIO TORQUE OUTER TERMINAL SCREWS: 0.5Nm / TORQUE GROUND NUTS: 2.5-3Nm NOTE 2 INPUT OUTPUT CONNECTION TERMINA AWG SIZE: 26-12 AWG | N. 4.5 in.lbs | | | | P | LTR | SEE SHEET | DESCRIPTION | | DATE | DWN | APVD | D |
| | AWG SIZE: 26-12 AWG WIRE SECTION: 4 mm ² THREADED BOLT SIZE FOR GROUND: M6 | | | | | | | | | | | | | |
| | NOTE 3 SUPPLIED WITH DIN RAIL BRACKET | | | | | | | | | | | | | |
| | NOTE 4 DRAWINGS SHOWS DIN RAIL FOR REFEERENCE ONLY | | | | | | | | | | | | | |
| C | | | | | | U 2 3 E | o LINE O | LOAD | | 122 | | | | С |
| В | Pelle C | | | | | RAIL | СНА | | | 35 BRACKET | | | - | B |
| А | FRONT SIDE | REAR SIDE | THIS DRAWING IS DIMENSIONS: mm MATERIAL | TOLERANC OTHERWISE | SPECIFIED: APVD CL - PROD 0.5 0.40 0.130 APPL ±- WEIG | <u>PAT</u> SA IRISBC UCTSPEC - ICATIONS - HT | OLIF SPEC | P D 8 size A 3 | OWER LINE FI IN 35 RAIL I KEMS10AFPDVN cage code drawing no 00779 C=7- | ILTER FOR INSTALLATIO 0 | R | , ESTRICTE _ REV | | A |

470-19 (3/13)

