

LINE SIDE

D

С

В

А


L1 G-

L2 G-

L3 🗕

E

 \bigoplus



≷

ξ


≩

	2									
		REVISIONS								
		P LTR	DESCRIPTION	DATE	DWN	APVD				
-0 1 ′		A INITIAL RE	LEASE	07APR2021	SB	СВ				
• [1							- C			
-● L2′ LOAD SIDE	THE LISTED	WILL BE FORMALL' AGENCY. THEREFORE	Y RECOGNIZED, CERTIFIED O E, ALL TEST/REQURIEMENTS DWING AGENCY STANDARDS WI	SPECIFIED) IN T	THE				
-• L3′	UL APPROVED 30A 440V 50Hz/60Hz 40°C CSA APPROVED 30A 440V 50Hz/60Hz 40°C									
	<u>OPERATING_SPECIFICATION</u> LINE CURRENT/VOLTAGE: 30A, 440VAC LINE FREQUENCY: 50/60Hz									
	MAXIMUM LEAKAGE CURRENT: 5mA @ 230VAC, 50Hz									
-0 [OPERATING AMBIENT TEMPERATURE RANGE @ RATED CURRENT: -25°C TO +40°C									
₽	IN AN AMBIENT, Ta, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, Io, IS AS FOLLOWS: Io=Ir- $\sqrt{\frac{85-Ta}{45}}$									
	STORAGE TEM	<u>' specifications</u> 1perature: -40°C t 21 days @ 40°C and	• • + 85°C							
2	<u>test specif</u> Inductance,	<u>ICATIONS</u> NOMINAL: 2.4mH								
34 13 20 28		:@1kHz DUND, NOMINAL:0.: NE, NOMINAL:1µF	3μF							
EL TO TE	DISCHARGE R L/G I.R. 68 L/L I.R. L/N I.R. XX N/G I.R. XX IR (NO DISC	30KΩ 1W 3MΩ 1W KX KX	20°C, 50% RH AND 100VDC, 1	MIN: 6MQ			E			
ING SPECIFICATION	RECOMMENDED RECEIVING INSPECITON HIPOT LINE TO GROUND FOR 1 MINUTE: 2632VDC LINE TO LINE FOR 1 MINUTE: 1892VDC									
		Y TO SELECT AND (QUALIFY A FILTER IS FOR Y I IN YOUR EQUIPMENT.	OUR						
		07,APR2021								
THIS DRAWING IS A CONTROLLED D	ВАРА	T SAHAS 07APR2021 S BOLLE	ETE TE	Connectivit	у					
DIMENSIONS: TOLERANCE OTHERWISE MM	SPECIFIED APVD	07APR2021 NAME	OWER LINE FILTER FOR				1			
0 PLC ±- 1 PLC ±0 2 PLC ±0	DDODUCT	SPEC	OIN 35 RAIL INSTALLATI BOKEMS10ABSDVM	ON			,			
4 PLC ±0 ANGLES	.0500 ±-	SIZE			RESTRIC	TED TO	1			
MATERIAL FINISH	WEIGHT	1 1 0	300779C=8-1609967-6		-	,				
	CUSTOM	IER DRAWING	scale 1:2	heet OF	P REV	Á	J			




SCHEMATIC

M H z	0.01	0.05	0.15	0.5	1	3	5	10	30
СМ	40	26	47	70	73	51	44	34	1 3
DM	28	21	37	76	82	67	49	20	28



470-19 (3/13)



|470-|9 (3/|3)