



LP 6.2 WIRE-TO-BOARD POWER CONNECTOR

POWER SOLUTION DELIVERING RELIABLE HIGH-CURRENT PERFORMANCE

The LP 6.2 wire-to-board power connector offers a more reliable solution for PCB manufacturers, addressing the demanding needs of high current applications. Capable of supporting up to 14A and featuring an innovative external-locking mechanism, this connector is excellent for a wide range of power-intensive applications, including HVAC systems, home appliances, and industrial equipment. The LP 6.2 connector offers seamless compatibility with similar 6.2mm pitch connectors, enabling quick adaptability and reducing the need for costly redesigns. Its external-locking design enhances mating reliability and efficiency, helping ensure secure connections in even challenging environments. Additionally, the LP 6.2 connector meets the UL 94 V-0 flammability standard and achieves a Glow Wire Test (GWT*) rating of 750°C, providing robust safety protection and durability for high-performance applications.

ELECTRICAL

- Rated Current: 14A Max
- Rated Voltage: 600V AC/DC

MECHANICAL

- Centerline (mm): 6.2
- Number of Positions: 3P
- Wire Size: 18-14 AWG

MATERIALS

- Operating Temperature (°C): -40 to +90
- Housing Flammability Ratings: UL 94 V-0 and GWT* 750°C
- Contact: Copper alloy/brass

PRODUCT COMPLIANCE CERTIFICATION

- UL E28476

FEATURES

- Provide 14A high current performance by utilizing high-conducting material terminal
- Features an external-locking structure to improve mating efficiency and connection stability
- Designed for quick adaptability with similar 6.2mm pitch connectors
- Connector meets UL 94 V-0 flammability requirements and achieves a Glow Wire Test (GWT*) rating of 750°C for enhanced safety and durability

ADDITIONAL INFORMATION

- Product Specification: [108-161340](#)
- Application Specification: [114-160996](#)
- [Product Pages](#)

APPLICATIONS



Air
Conditioning



Washing
Machine



HVAC
Equipment



Industry
Machine

*GWT refers to glow wire testing. For more information on glow wire testing please review the white paper [Glow Wire Testing for the Appliance Industry](#) or visit the [Glow Wire Capable Connectors product page](#).

LP 6.2 WIRE-TO-BOARD POWER CONNECTOR

PART NUMBER

Header & Plug Housing

Part Number	Position	Type
2487504-3	3P	Header
2487511-3	3P	Plug

Contact

Part Number	Wire Size (AWG)	Material
2487512-1	18-14	Copper alloy
2487512-2	18-14	Brass

FOR MORE INFORMATION

ASK OUR EXPERT ►

te.com/lp-6.2-wire-to-board-power-connector

TE Connectivity, TE connectivity (logo) and TE are trademarks owned or licensed by the TE Connectivity plc family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

© 2025 TE Connectivity. All Rights Reserved.

04/25