



0.8 MM LOW-PROFILE IDC CONNECTOR SYSTEM

Meeting the industry need for small centerline wire-to-board connectors with a convenient insulation displacement contact (IDC) termination, 0.8 mm low-profile IDC connectors can be used in space constrained applications where signal or low power needs to be routed through a device.

PRODUCT FEATURES

- Compact 0.8 mm centerline
- Convenient IDC cable termination
- Current rating: 1A
- High temperature plastic, UL94V-0
- Gold plating options available

PRODUCT BENEFITS

- Space-saving, low-profile design
- Convenient IDC cable termination
- Helps save PCB real estate
- Competitive pricing and fast delivery

APPLICATIONS

Internet of Things (IoT):

- Security systems
- Small appliances
- Smart meters
- Vending machines

Data communications:

- Servers
- Switches
- Modems

Consumer devices

Automotive:

- Control units
- Infotainment systems

Medical:

- Patient monitors

Industrial automation

0.8 MM LOW-PROFILE IDC CONNECTOR SYSTEM

PART NUMBERS

Part Number	Detailed Description
2483180-2	0.8 mm Low-profile IDC Header Straight WTB 2 Position
2483180-3	0.8 mm Low-profile IDC Header Straight WTB 3 Position
2483180-4	0.8 mm Low-profile IDC Header Straight WTB 4 Position
2483180-5	0.8 mm Low-profile IDC Header Straight WTB 5 Position
2483180-6	0.8 mm Low-profile IDC Header Straight WTB 6 Position
1-2483180-0	0.8 mm Low-profile IDC Header Straight WTB 10 Position
1-2483180-2	0.8 mm Low-profile IDC Header Straight WTB 12 Position
2483190-2	0.8 mm Low-profile IDC Header Right Angle WTB 2 Position
2483190-3	0.8 mm Low-profile IDC Header Right Angle WTB 3 Position
2483190-4	0.8 mm Low-profile IDC Header Right Angle WTB 4 Position
2483190-5	0.8 mm Low-profile IDC Header Right Angle WTB 5 Position
2483190-6	0.8 mm Low-profile IDC Header Right Angle WTB 6 Position
2483190-8	0.8 mm Low-profile IDC Header Right Angle WTB 8 Position
1-2483190-0	0.8 mm Low-profile IDC Header Right Angle WTB 10 Position
1-2483190-2	0.8 mm Low-profile IDC Header Right Angle WTB 12 Position
2483193-2	0.8 mm Low-profile IDC Receptacle WTB 2 Position
2483193-3	0.8 mm Low-profile IDC Receptacle WTB 3 Position
2483193-4	0.8 mm Low-profile IDC Receptacle WTB 4 Position
2483193-5	0.8 mm Low-profile IDC Receptacle WTB 5 Position
2483193-6	0.8 mm Low-profile IDC Receptacle WTB 6 Position
2483193-8	0.8 mm Low-profile IDC Receptacle WTB 8 Position
1-2483193-0	0.8 mm Low-profile IDC Receptacle WTB 10 Position
1-2483193-2	0.8 mm Low-profile IDC Receptacle WTB 12 Position
1-2483193-4	0.8 mm Low-profile IDC Receptacle WTB 14 Position
1-2483193-6	0.8 mm Low-profile IDC Receptacle WTB 16 Position

te.com

TE Connectivity, TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty, or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2024 TE Connectivity. All Rights Reserved.

08-24