



Safety Products Light Curtains & Safety Relays

November 2023

EVERY CONNECTION COUNTS



Agenda

INTRODUCTION

- Basics on safety

PROJECT SCOPE

SAFETY LIGHT CURTAINS

- Concept & features
- Product scope
- Accessories

SAFETY INTERFACES

- Concept & features
- Product scope

MARKETING COLLATERALS

CONCLUSION



BASICS ON SAFETY

EVERY CONNECTION COUNTS



WHAT IS SAFETY?

Machinery Safety

Machinery safety is the basis for secure cooperation between human and machine. The use of secure automation helps **protect staff** from the **hazards** that emanate **from plant and machinery**, enables smooth operation and helps increase production quality.

Machinery safety refers to the practices, measures, and standards put in place to help ensure the well-being of individuals interacting with machines.



WHAT IS SAFETY?

Safety

Active protective measures are usually implemented by **selecting** and **combining** in an appropriate way hardware components (such as sensors, switches, logic units, relays etc.) to build up a **Safety Related Control System**

A **control system** that executes an **active protective measure** is said to carry out a **safety function** and the control system itself is called **Safety Related Control System**.



Safety function	Example of application
Safety –related stop function initiated by a safeguard	Stop a motor in response to tripping of a protective device
Manual reset function	Intended action to re-establishes the safeguard after its actuation. Acknowledgement that risk is no more present
Start/restart function	Start of a dangerous movement can take place only when an hazardous situation no more exists
Muting function	Automatic temporary suspension of a safety function
Hold-to-run function	Hazardous machine movements can be controlled from a position within the hazard zone, e.g., inching mode during setup
Prevention of unexpected start-up	Keeping a machine in a stopped condition while persons are present in danger zones
Operating mode selection	Activation of safety functions by an operating mode selector switch
Safe motion, safe position	Overspeed, overtravel control

WHAT IS SAFETY?

Main standards Europe

Fundamental product European directives :

2006/42/EC: “Machine Directive” → for machine manufacturers

2014/30/EU: “Electromagnetic Compatibility Directive” → applies to electrical & electronic devices

2014/35/EU: “Low Voltage Directive” → Applies to electrical equipment from 50 V to 1500 V

Umbrella machinery safety standards

ISO 13849 “Safety of machinery”

IEC 61508 “Functional safety of electrical / electronic / programmable electronic safety related systems” which impacts safety of machinery especially through

IEC 62061 “Safety of machinery - Functional safety of safety-related electrical, electronic and programmable electronic control systems”


IEC 61496 “Safety of machinery – Electro-sensitive protective equipment

Main standards North America

Health & Safety is governed by **OSHA** (Occupational Health and Safety Administration)

ANSI (American National Standard Institute) issue standards on the safety of machine tools and construction

Underwriters Laboratories Inc (UL) or **CSA** are the bodies that issue certifications for safety equipment



A type C Standard takes priority over type A and B Standards

WHAT IS SAFETY?

Safety levels

SAFETY LEVEL

TYPE 4

SIL 3 - SILCL 3 | PL e - Cat. 4

TYPE 2

SIL 1 - SILCL 1 | PL c - Cat. 2

SIL (Safety Integrity Level) as per EN 62061

Can only be used for electrical, electronic or programmable safety solutions.

PL (Performance Level) as per EN ISO 13849-1

is a technology-neutral concept that can be used for electrical, mechanical, pneumatic and hydraulic safety solutions.

Category : refers to the machine itself and achievable PL.

Goes from category B (basic) to category 4 (highest).

Ex: Category 4 allow to reach PL e (highest protection against higher risk)

Type : refers to the specific design of protection equipment like a safety light curtain or relay.

Type 4 device would be most likely to be used in a category 4 application, and a Type 2 light curtain could probably only be used for a category 2 application



SIL is particularly **well-suited to large, complex facilities or factories** with multiple machines, while **PL** is **suitable for individual machines**.

WHAT IS SAFETY?

RISK EVALUATION : **PLr** (**P**rotection **L**evel **r**equired)


Machinery Directive - Overview of the steps to achieve the level of safety required by each application

▼ Objective: risk reduction by applying defined control measures



How to determine the required performance level – PLr:

- S = severity of the damage:
 - S1= light damage– reversible;
 - S2= serious damage– irreversible.
- F = frequency and/or danger exposition:
 - F1= rare and/or for a limited time;
 - F2= frequent/continuous and/or for an extended period of time.
- P = possibility of avoiding the danger or limiting the damage:
 - P1= possible within certain conditions;
 - P2= hardly possible.



PLr(e) provides the greatest contribution to risk reduction

PROJECT SCOPE

EVERY CONNECTION COUNTS



Product portfolio

SAFETY LIGHT CURTAINS

SLC4 Range



SAFETY LEVEL

TYPE 4
SIL 3 - SILCL 3 | PL e - Cat. 4

SLC2 Range



SAFETY LEVEL

TYPE 2
SIL 1 - SILCL 1 | PL c - Cat. 2

SAFETY INTERFACES

SRS - SRK RANGE




SINGLE & MULTI-FUNCTION SAFETY RELAYS

Type 4 SIL 3 - SILCL 3 | PL e - Cat. 4
OR
Type 2 SIL 1 - SILCL 1 | PL c - Cat. 2

SAFETY LIGHT CURTAINS

SLC Range

EVERY CONNECTION COUNTS



response time ≤ 4.5 ms
consumption 1 W
temperature range -10 to $+5$ °C
K512310000
TE Connectivity
IP65
IP67
Made in Italy

TE
connectivity

Safety Light Curtain : Principle of operation

The SLC uses a combination of an **emitter** and a **receiver**. Multiple **parallel beams** are emitted with various **resolutions** (distance between beams).

If no object or people are blocking the beam between the emitter and receiver, the machine is in a secure state and is allowed to operate.

On the other hand, **if any or all** of the light beams are **blocked by a human finger, hand or body**, the machine determines the situation to be hazardous and **turns off** the output of the receiver to stop the machine.

SLC's are considered as **sensors**



Emitter Receiver



Safety Light Curtain : Advantages

- Effective protection in **the event of fatigue or distraction** of the operator.
- Increase in the productive capacity of the machine as the SLC **does not require** the manual handling of physical guards or waiting for them to open.
- **Faster** machine loading/unloading operations.
- **Reduced times** of approach to the working areas.
- **Virtually elimination risk of tampering** since any irregular intervention on the light curtain stops the machine.
- **Simple and quick installation**, with greater flexibility of adjustment on the machine, even in the case of subsequent repositioning.
- Possibility **to build up large sized protections**, either **linear** or **along a perimeter**, on several sides, at **greatly reduced costs**.
- **Facilitated and fast maintenance** of the machine, as there is **no need to remove physical guards**, such as grids, gates, etc.
- **Improved appearance** and **ergonomic** effectiveness of the machine.



Safety Light Curtain : Main Characteristics

SAFETY LEVEL

SAFETY LEVEL

TYPE 4

SIL 3 - SILCL 3
PL e - Cat. 4


SAFETY LEVEL

TYPE 2


SIL 1 - SILCL 1
PL c - Cat. 2

RESOLUTION

FINGER resolution 14 mm	HAND resolution 20 mm-30 mm-40 mm
BODY resolution 50 mm-90 mm	ACCESS CONTROL 2-3-4 beams



PROTECTED HEIGHT RANGE PROTECTED ZONE



RESPONSE TIME



SLC4 Type 4 Safety Light Curtain

Main features

SLC4



4 types of detection    

6 resolutions :

- 14 mm for finger detection
- 20 mm, 30 mm, 40 mm for hand detection
- 50 mm, 90 mm for detection of the body in a dangerous area

Access control : 2-3-4 beams for body detection

Protected height range 160 mm to 2250 mm

Maximum range:


- Selectable 3 m to 6 m for 14 mm resolution models (finger)
- Selectable 4 m to 12 m for other models (hand & body)
- Selectable 10 m to 20 m for L versions

Integrated manual or automatic Start/Restart

Feedback input for external relay monitoring

M12 5/8 poles connectors


Use of unshielded cables up to 100m



SLC4 Type 4 Safety Light Curtain

Models with automatic restart, integrated functions and longer range

SLC4



SLC4...

Manual/Automatic Start/Restart

Feedback input - EDM

Connectors: M12/5 (Emitter), M12/8 (Receiver)

Max range: 6 m (14 mm), 12 m (20 mm, 30 mm, 40 mm, 50 mm, 90 mm and 2-3-4 beams)

SLC4...L

Manual/Automatic Start/Restart

Feedback input - EDM

Connectors: M12/5 (Emitter), M12/8 (Receiver)

Max range: 20 m for 20 mm, 30 mm, 40 mm, 50 mm, 90 mm and 2-3-4 beams

SAFETY LEVEL

TYPE 4

SIL 3 - SILCL 3
PL e - Cat. 4

Type 4	IEC 61496-1-2
Category 4	ISO/EN 13849-1
PL e	ISO/EN 13849-1
SIL 3	IEC 61508
SIL CL 3	EN 62061



SLC2 Type 2 Safety Light Curtain

Manual/Automatic Start/Restart



SLC2...

3 types of detection



4 Resolutions

- 30 mm - 40 mm for hand detection
- 50 mm - 90 mm for detection of the body in a dangerous area

Access control : 2-3-4 beams for body detection

Protected height range 160 mm to 2250 mm

Max range 12 m (20 mm, 30 mm, 40 mm, 50 mm, 90 mm and 2-3-4 beams)

Integrated manual or automatic Start/Restart

Feedback input for external relay monitoring

M12 5/8 poles connectors

Use of unshielded cables up to 100 m

SAFETY LEVEL

TYPE 2

SIL 1 - SILCL 1
PL c - Cat. 2

- Type 2 IEC 61496-1:2004
IEC 61496-2:2006
- Category 2 ISO/EN 13849-1:2008
- PL c ISO/EN 13849-1:2008
- SIL 1 IEC 61508-1:1998
IEC 61508-2:2000
- SIL CL 1 EN 62061:2005



One simple product range to cover wide range of today's industrial applications

Reliable and compact

High ingress protection ratings

IP67 and IP65 supports protection against dirt, dust, sand, water, projections and other liquids with IP67 and IP65 ratings. High resistance to infiltration by dust and liquids in a highly compact light curtain

Compact size

SLC is one of the smallest light curtains in the market (with integrated safety functions) With a minimal cross section: 28 mm x 30 mm

Robustness

Thanks to powder-coated aluminum casing, SLC range can obtain high level of reliability. Also, highly reliable in cold storage facilities with -30° C to +55° C operating temperature

Safe and Smart

Virtually no blind area

Thanks to the position of the 1st beam on the connector side, this helps protected area to extend until the light curtain end and maintain the resolution

Fast, simple installation

Plug and play thanks to the M12 connectors and the use of unshielded cables. Virtually no programming necessary Easy to install and replace

User-friendly diagnostics via

LEDs Status indicating display that including alignment aids are helping the user to diagnose the status

High level of productivity and safety

High Safety grades

Type 2 and Type 4 SLC light curtains approved in accordance with;

- EN IEC 61496-1/-2
- ANSI / UL 1998

Finger, hand and body protection

From safety light barriers supporting body protection to the light safety light curtain for higher finger and hand protection, the product series SLC4 and SLC4 cover a large portfolio

A range updated to your needs

Integrated safety functions, including self-monitoring of static outputs, control of external contactors (EDM) and selectable automatic/manual restart, supports increased productivity due to reduced downtimes

Reliable and compact


High ingress protection ratings IP67 and IP65

- Helps protect against dirt, dust, sand, water, projections and other liquids
- Resistance to infiltration by dust and liquids in a highly compact light curtain



Compact size

SLC is one of the smallest light curtains in the market (with integrated safety functions) With a minimal cross section: 28 mm x 30 mm



Robustness


Thanks to powder-coated aluminum casing SLC range can obtain high level of mechanical reliability. Also, highly reliable in cold storage facilities with -30° C to +55° C operating temperature



Safe and Smart


Virtually no blind area

Thanks to the position of the 1st beam on the connector side, this helps protected area to extend until the light curtain end and maintain the resolution.



Fast, simple installation

Plug and play, easy to install & replace thanks to the M12 connectors
Unshielded cables.







User-friendly diagnostics via LEDs

Status indicating display that including alignment aids are helping the user to diagnose the status

Safe and Smart : Virtually no blind area on one side


- 1 Thanks to the position of the 1st beam, The protected area extends until the light curtain end maintaining the finest resolution up to (14 mm)
- 2 Fingers and hands are always detected and protected on the entire height
- 3 2 L-mounted light curtains maintain 40 mm resolution (hand detection) in corner (models with resolution 30 mm and 40 mm)




User interface

Pin-out and display information

Pin-out (X/XH models)



Display information




On the receivers of 14 mm resolution and H models a blue LED indicates a weak signal intensity.

During alignment operations, checking the blue LED status can be helpful. During standard operation it must remain off.


Emitter - All models

Three colour LED	Meaning
	System power-on - Initial TEST
	System power-on - HIGH working range selected
	FAIL condition - The type of fault is identified by the number of flashes - See technical manual
	TEST condition
	Normal operating condition



Receiver - All models except SLC4 14 mm and L (range 20 m) versions

1 - Yellow LED	2 - Two colour LED	Meaning
		System power-on - Initial TEST
		BREAK condition
		CLEAR condition - SLC4 (with integrated control functions) only
		BREAK_K condition - SLC4 (with integrated control functions) only
		GUARD condition
		FAIL condition - The type of fault is identified by the number of flashes - See technical manual



SAFETY RELAYS

SRS-SRK Range

EVERY CONNECTION COUNTS



Safety Relays

...for barriers with automatic start/restart (SLC series)

SRS safety relays

The Safety Relays are a dedicated interface between safety light curtains, equipped with self-controlled safety static outputs, and control circuits of the machine or plant




- SRS-2NO-1NC → Safety interface for devices with integrated feedback input for EDM (with auxiliary contact). 2 NO + 1 NC. Screw Terminal Blocks
- SRS-2NO → Safety interface for devices with integrated feedback input for EDM. 2 NO. Screw Terminal Blocks

- SRS4-2NO → Safety interface for OSSD output devices. 2 NO. Screw Terminal Blocks
- SRS4M-2NO → Safety interface with integrated Muting functions for OSSD output devices. 2 NO. Screw Terminal Blocks
- SRS MULTI → Multifunction Safety Relay, Screw Terminal Block

(Safety Light Curtains, Solid-State-Output Devices (i.e. RFID safety switches), Dual-Channel Emergency Stops, Two-Hand Controls and Safety, Photocells)

How is it functioning?

Safety relays are devices used to control the safety-related part of control systems in such a way that machine operation is only allowed when safety is confirmed. It supports safety by controlling signals coming from inputs, especially emergency stop switches and locking switches and controls the contactors and other devices connected to the outputs according to the results of this detection. In other words, the safety relay module and safety controller play a central role as the logic unit in the safety-related part of the control system.




Typical applications

- Robotics
- Food & beverage
- Packaging
- Pharmaceuticals
- Paper
- Logistics
- Metalworking
- Woodworking
- Chemicals
- Injection moulding
- Printing



AFG- Robotics, Machinery, Control cabinet


Safety area with light curtains and mirrors



Safety area with light curtains for machinery



Safety solution for OEM machine builders




Safety systems for robots
Safe Robotics Area supports protection, safer access to cooperative robot applications for less downtime, enhanced work processes and higher productivity.

Marketing Materials

TE.COM

Product sheet




CVM Samples



Technical guides

Manuals and Quick guides



Media

Datasheets, Catalogue page



Demokit

Demo kits



Training Materials

1. Webinars
2. Training PPT
3. Customer PPT



© 2023 TE Connectivity Ltd. All Rights Reserved

TE Connectivity, TE, TE connectivity (logo) and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity Ltd. family of companies.

All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any changes to the information contained herein without prior notice. TE Connectivity assumes only those obligations set forth in the terms and conditions for this product and shall in no event be liable for any incidental, indirect, or consequential damages arising out of the sale, resale, use, or misapplication of the product. TE expressly disclaims any implied warranties with respect to the information contained herein, including, but not limited to, implied warranties of merchantability or fitness for a particular purpose. Dimensions, specifications and/or information contained herein are for reference purposes only and are subject to change without notice. Consult TE for the latest dimensions, specifications and/or information. Users of TE Connectivity products must make their own assessment as to whether the respective product is suitable for the respective desired application.

**CONNECT
LIKE THE WORLD
DEPENDS ON IT.
BECAUSE IT DOES.**

EVERY CONNECTION COUNTS

